









THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>(PG9)</p>  <p>Recommended Panel Cut-Out</p> </div> <div style="text-align: center;"> <p>(M16*1.5)</p>  <p>Recommended Panel Cut-Out</p> </div> </div>					<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th>REV.</th> <th>ECN NO.</th> <th>DATE</th> <th>SIGN</th> <th>DESCRIPTION</th> </tr> <tr> <td>B</td> <td>LEN1570203-210 LE31570188-191</td> <td>2015/07/17</td> <td>Yulong_wang</td> <td>Change to Shore Drawing.</td> </tr> <tr> <td>C</td> <td>LEN1680907-918</td> <td>2016/08/06</td> <td>Yulong_wang</td> <td>Add 6Pin & IP69K.</td> </tr> </table>	REV.	ECN NO.	DATE	SIGN	DESCRIPTION	B	LEN1570203-210 LE31570188-191	2015/07/17	Yulong_wang	Change to Shore Drawing.	C	LEN1680907-918	2016/08/06	Yulong_wang	Add 6Pin & IP69K.																																										
REV.	ECN NO.	DATE	SIGN	DESCRIPTION																																																										
B	LEN1570203-210 LE31570188-191	2015/07/17	Yulong_wang	Change to Shore Drawing.																																																										
C	LEN1680907-918	2016/08/06	Yulong_wang	Add 6Pin & IP69K.																																																										
<p>M 12A - XX P F F S - S F 8 XXX</p> <p>12A: A-Code</p> <p>03: 3Pin 04: 4Pin 05: 5Pin 06: 6Pin 08: 8Pin 10: 10Pin 12: 12Pin</p> <p>P: Panel (板端) F: Female Connector (母座)</p> <p>001: PG9 002: M16*1.5 8: IP68/69K (防水等级68/69K) F: Front Fasten (前鎖式/Enclosure Rear Mount) S: Screw (螺絲式) S: Solder Type (焊接式) F: Female Pin (母Pin)</p>																																																														
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>M12A-03PFFS-SF8XXX</td> <td>2.5</td> <td></td> </tr> <tr> <td>M12A-04PFFS-SF8XXX</td> <td>2.5</td> <td></td> </tr> <tr> <td>M12A-05PFFS-SF8XXX</td> <td>2.5</td> <td></td> </tr> <tr> <td>M12A-06PFFS-SF8XXX</td> <td>2.5</td> <td></td> </tr> <tr> <td>M12A-08PFFS-SF8XXX</td> <td>2.5</td> <td></td> </tr> <tr> <td>M12A-10PFFS-SF8XXX</td> <td>4.5</td> <td>2.5</td> </tr> <tr> <td>M12A-12PFFS-SF8XXX</td> <td>4.5</td> <td>2.5</td> </tr> <tr> <td>Item No.</td> <td>A</td> <td>B</td> </tr> <tr> <td></td> <td colspan="2" style="text-align: center;">Pin伸出長度</td> </tr> </table>				M12A-03PFFS-SF8XXX	2.5		M12A-04PFFS-SF8XXX	2.5		M12A-05PFFS-SF8XXX	2.5		M12A-06PFFS-SF8XXX	2.5		M12A-08PFFS-SF8XXX	2.5		M12A-10PFFS-SF8XXX	4.5	2.5	M12A-12PFFS-SF8XXX	4.5	2.5	Item No.	A	B		Pin伸出長度		<p>Note:</p> <ul style="list-style-type: none"> * Important Dimension. * Waterproof Rate: IP68, IP69K. * Housing: Nylon+GF, Black. * Female Pin: Copper Alloy, Gold Plated. * Shield: Zinc Alloy, Nickel Plated. * Screw Nut: Zinc Alloy, Nickel Plated. * Panel O-Ring: Viton, Black. * Housing O-Ring: Viton, Green. * Rated Voltage: 3 & 4Pin 250V dc. or ac. 5Pin 60V dc. or ac. 6-12Pin 30V dc. or ac. * Rated Current: 3-5Pin 4A 6-8Pin 2A 10-12Pin 1.5A * Operating Temperature: -40-105°C * For Panel Thickness Max 4.5mm. * Recommended Nut Torque: 4-6 Kgf.cm. 																															
M12A-03PFFS-SF8XXX	2.5																																																													
M12A-04PFFS-SF8XXX	2.5																																																													
M12A-05PFFS-SF8XXX	2.5																																																													
M12A-06PFFS-SF8XXX	2.5																																																													
M12A-08PFFS-SF8XXX	2.5																																																													
M12A-10PFFS-SF8XXX	4.5	2.5																																																												
M12A-12PFFS-SF8XXX	4.5	2.5																																																												
Item No.	A	B																																																												
	Pin伸出長度																																																													
 <p style="text-align: center;">Pin Assignment Front View</p>																																																														
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%;">UNIT: mm</td> <td style="width: 10%;"></td> <td colspan="2" style="width: 40%;">TITLE M12 A-Code Female Conn. Solder Front Type</td> <td colspan="2" style="width: 20%; text-align: center;">Amphenol LTW</td> <td style="width: 10%;">ITEM NO</td> <td style="width: 10%;">DRAWN BY</td> <td style="width: 10%;">DATE</td> </tr> <tr> <td>TOLERANCE</td> <td></td> <td>SCALE</td> <td>SIZE</td> <td colspan="2" rowspan="2" style="text-align: center;">安費諾亮泰企業股份有限公司</td> <td>DRG NO</td> <td>Yulong_wang</td> <td>2016-08-06</td> </tr> <tr> <td>.X ±0.25</td> <td></td> <td>3:2</td> <td>A4</td> <td>SHEET 1 OF 1</td> <td>M12A-XXPFFS-SF8XXX</td> <td>CHECKED BY</td> <td>Jinhai</td> <td>2016-08-06</td> </tr> <tr> <td>.XX ±0.1</td> <td></td> <td>REV. C</td> <td>MC-REV. A.5</td> <td colspan="2"></td> <td>CUSTOMER</td> <td>APPROVED BY</td> <td>Jerry</td> <td>2016-08-06</td> </tr> <tr> <td>.XXX ±0.05</td> <td></td> <td></td> <td></td> <td colspan="2"></td> <td></td> <td></td> <td></td> </tr> <tr> <td>ANGLES ±1°</td> <td></td> <td></td> <td></td> <td colspan="2"></td> <td></td> <td></td> <td></td> </tr> </table>				UNIT: mm		TITLE M12 A-Code Female Conn. Solder Front Type		Amphenol LTW		ITEM NO	DRAWN BY	DATE	TOLERANCE		SCALE	SIZE	安費諾亮泰企業股份有限公司		DRG NO	Yulong_wang	2016-08-06	.X ±0.25		3:2	A4	SHEET 1 OF 1	M12A-XXPFFS-SF8XXX	CHECKED BY	Jinhai	2016-08-06	.XX ±0.1		REV. C	MC-REV. A.5			CUSTOMER	APPROVED BY	Jerry	2016-08-06	.XXX ±0.05									ANGLES ±1°												
UNIT: mm		TITLE M12 A-Code Female Conn. Solder Front Type		Amphenol LTW		ITEM NO	DRAWN BY	DATE																																																						
TOLERANCE		SCALE	SIZE	安費諾亮泰企業股份有限公司		DRG NO	Yulong_wang	2016-08-06																																																						
.X ±0.25		3:2	A4			SHEET 1 OF 1	M12A-XXPFFS-SF8XXX	CHECKED BY	Jinhai	2016-08-06																																																				
.XX ±0.1		REV. C	MC-REV. A.5			CUSTOMER	APPROVED BY	Jerry	2016-08-06																																																					
.XXX ±0.05																																																														
ANGLES ±1°																																																														