

PRODUCT DATASHEET NAV 70 LED FIL V 5400LM 35W 727 E27

NAV LED FIL V | LED replacement for NAV lamps in design-oriented outdoor applications



Areas of application

- Streets
- Area lighting
- Pedestrian zones
- Parks
- Outdoor applications only in suitable luminaires

Product benefits

- Same design as traditional NAV lamps with frosted, ellipsoid full glass bulb
- Full use of reflector of existing luminaire thanks to 360 degree beam angle
- Saves up to 78 % energy when used as replacement for sodium vapor lamps (NAV)
- Instant 100 % light, no warm-up time
- Similar light distribution as traditional NAV lamps

Product features

- Suitable for operation with conventional control gear (CCG) or 230 V AC mains
- Very high efficiency of up to 190 lm/W
- Power factor: 0.9
- Type of protection: IP65
- Surge protection: up to 2 kV (L-N)




TECHNICAL DATA

Electrical data

Nominal wattage	35 W
Construction wattage	35.00 W
Nominal voltage	220240 V
Claimed equiv. conventional lamp power	70 W
Nominal current	155 mA
Type of current	AC
Inrush current	11.1 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	3
Max. lamp no. on circuit break. B10 A - CCG without compensation	4
Max. lamp no. on circuit break. B10 A - CCG with compensation	7
Max. lamp no. on circuit break. 16 A (B)	5
Max. lamp no. on circuit break. B16 A - CCG without compensation	6
Max. lamp no. on circuit break. B16 A - CCG with compensation	12
Total harmonic distortion	12 %
Power factor λ	> 0.90

Photometrical data

Luminous intensity	N/A
Luminous flux	5400 lm
Nominal useful luminous flux 90°	5400 lm
Luminous efficacy	154 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 К
Color rendering index Ra	70
Light color	727
Standard deviation of color matching	≤6 sdcm
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	1
Stroboscope effect metric (SVM)	0,4



Light technical data

Beam angle	360 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Rated beam angle (half peak value)	360.00 °

Dimensions & Weight

Overall length	210.00 mm
Diameter	38.00 mm
Maximum diameter	38 mm
Product weight	120.00 g

Temperatures & operating conditions

Ambient temperature range	-20+50 °C
Maximum temperature at tc test point	90 °C

Lifespan

Lifespan	25000 h
Number of switching cycles	100000
Lumen maintenance at end of serv	0.70
Rated lamp survival factor at 6,000	≥ 0.90

Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg

Mercury-free	Yes
Product remark	Available from June 2023

Capabilities

Dimmable	No

Certificates & Standards

Energy efficiency class	D ¹⁾
Energy consumption	35.00 kWh/1000h
Type of protection	IP65
Standards	CE / EAC / UKCA
Photobiological safety group acc. to EN62778	RG1

1) Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

Country-specific categorizations

Order reference	NAV 70 LED FIL

LOGISTICAL DATA

Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	E27
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	N/A
Networked standby power for CLS	N/A
Claim of equivalent power	No
Length	210.00 mm
Height	38.00 mm
Width	38.00 mm

Safety advice

- Not suitable for operation with ignitors
- Operation on the capacitor can lead to a reduction of the power factor of the system.
- When installed horizontally, the t $_{\rm c}$ point of the lamp is located on the top side of the lamp.
- Use in tight luminaires and luminaires with tight reflectors not recommended.
- Only suitable for temperatures of up to 50°C inside of the luminaire. Use in tight luminaires and luminaires with tight reflectors not recommended.

DOWNLOAD DATA

	Documents and certificates
PDF	User instruction
PDF	Declarations Of Conformity CE
PDF	Declarations Of Conformity UKCA
	Photometric and lighting design files
1	IES file (IES)
1	LDT file (Eulumdat)
1	UGR file (UGR table)
	LDC typ polar
1	Spectral power distribution

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854072017	Folding box 1	44 mm x 44 mm x 296 mm	170.00 g	0.57 dm ³
4099854072024	Shipping box 6	314 mm x 152 mm x 117 mm	1260.00 g	5.58 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.