


## Description

This series of fixed-voltage monolithic integrated-circuit voltage regulators is designed for a wide range of applications. These applications include on-card regulation for elimination of noise and distribution problems associated with single-point regulation. In addition, they can be used with power-pass elements to make high-current voltage regulators. Each of these regulators can deliver up to 100 mA of output current. The internal limiting and thermal shutdown features of these regulators make them essentially immune to overload. When used as a replacement for a Zener diode-resistor combination, an effective improvement in output impedance can be obtained together with lower-bias current.

## Features

- 3-Terminal Regulators
- Output Current Up to 100 mA
- No External Components
- Internal Thermal Overload Protection
- Internal Short-Circuit Limiting




**TO-92**

## Internal Block Diagram

## Package

TO-92: 1:GND 2:Input 3:Output



## Absolute Maximum Ratings

over operating temperature range (unless otherwise noted)

Parameter	79L05A thru 79L08A	79L12A THRU 79L18A	79L24A	Units
Input voltage	-30	-35	-40	V
Operating free-air, case, or virtual junction temperature range	0 to 150	0 to 150	0 to 150	°C
Storage temperature range	-65 to 150	-65 to 150	-65 to 150	
Lead temperature 1.6 mm (1/16 inch) from case for 10 seconds	260	260	260	

## Recommended Operating Conditions

Parameter	Min	Max	Units
Input voltage $V_i$	79L05A	-7	V
	79L06A	-8	
	79L08A	-10.5	
	79L12A	-14.5	
	79L15A	-17.5	
	79L18A	-20.5	
	79L24A	-27	
Output current, $I_o$		100	mA
Operating virtual junction temperature, $T_j$	0	125	°C

## Device Selection Guide

Output Voltage	Device
-5 V	79L05A
-6 V	79L06A
-8 V	79L08A
-12 V	79L12A
-15 V	79L15A
-18 V	79L18A
-24 V	79L24A

## Electrical Characteristics 79L05A

Electrical characteristics at specified virtual junction temperature,  $V_i = -10V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L05A			Units
		Min	Typ	Max	
Output voltage**		25°C	-4.8	-5	V
	$I_o = 1mA$ to 40 mA, $V_i = -7V$ to -20V	0°C to 125°C	-4.75		-5.25
	$I_o = 1mA$ to 70mA,		-4.75		-5.25
Input regulation	$V_i = -7V$ to -20V	25°C		15	mV
	$V_i = -8V$ to -20V			12	
Ripple rejection	$V_i = -8V$ to -18V, $f = 120Hz$	25°C	41	49	dB
Output regulation	$I_o = 1mA$ to 100mA	25°C		20	mV
	$I_o = 1mA$ to 40mA			10	
Output noise voltage	$f = 10Hz$ to 100 KHz	25°C		40	µV
Dropout voltage		25°C		1.7	V
Bias current		25°C		6	mA
		125°C		5.5	
Bias current change	$V_i = -8V$ to -20V	0°C to 125°C		1.5	
	$I_o = 1mA$ to 40mA			0.1	

## Electrical Characteristics 79L06A

Electrical characteristics at specified virtual junction temperature,  $V_i = -11V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L06A			Units
		Min	Typ	Max	
Output voltage**		25°C	-5.75	-6	-6.25
	$I_o = 1mA$ to 40 mA, $V_i = -8V$ to -20V	0°C to 125°C	-5.7		-6.3
	$I_o = 1mA$ to 70mA,				
Input regulation	$V_i = -8V$ to -20V	25°C		20	175
	$V_i = -9V$ to -20V			15	125
Ripple rejection	$V_i = -9V$ to -19V, $f = 120Hz$	25°C	40	48	
Output regulation	$I_o = 1mA$ to 100mA	25°C		21	80
	$I_o = 1mA$ to 40mA			11	40
Output noise voltage	$f = 10Hz$ to 100 KHz	25°C		44	
Dropout voltage		25°C		1.7	
Bias current		25°C			6
		125°C			5.5
Bias current change	$V_i = -9V$ to -20V	0°C to 125°C			1.5
	$I_o = 1mA$ to 40mA				0.1

\* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33μF capacitor across the input and a 0.1 μF capacitor across the output.

\*\* This specification applies only for dc power dissipation permitted by absolute maximum ratings.

## Electrical Characteristics 79L08A

Electrical characteristics at specified virtual junction temperature,  $V_i = -14V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L08A			Units
		Min	Typ	Max	
Output voltage**		25°C	-7.7	-8	-8.3
	$I_o = 1mA$ to 40 mA, $V_i = -10.5V$ to -23V	0°C to 125°C	-7.6		-8.4
	$I_o = 1mA$ to 70mA,				
Input regulation	$V_i = -10.5V$ to -23V	25°C		42	200
	$V_i = -11V$ to -23V			36	150
Ripple rejection	$V_i = -11V$ to -21V, $f = 120Hz$	25°C	37	46	
Output regulation	$I_o = 1mA$ to 100mA	25°C		30	100
	$I_o = 1mA$ to 40mA			15	50
Output noise voltage	$f = 10Hz$ to 100 KHz	25°C		54	
Dropout voltage		25°C		1.7	
Bias current		25°C			6
		125°C			5.5
Bias current change	$V_i = -11V$ to -23V	0°C to 125°C			1.5
	$I_o = 1mA$ to 40mA				0.1

## Electrical Characteristics 79L12A

Electrical characteristics at specified virtual junction temperature,  $V_i = -19V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L12A			Units	
		Min	Typ	Max		
Output voltage**		25°C	-11.5	-12	-12.5	V
	$I_o = 1mA$ to $40mA$ , $V_i = -14.5V$ to $-27V$	0°C to 125°C	-11.4		-12.6	
	$I_o = 1mA$ to $70mA$		-11.4		-12.6	
Input regulation	$V_i = -14.5V$ to $-27V$	25°C	50	250	mV	
	$V_i = -16V$ to $-27V$		40	200		
Ripple rejection	$V_i = -15V$ to $-25V$ , $f = 120Hz$	0°C to 125°C	37	42		dB
Output regulation	$I_o = 1mA$ to $100mA$	25°C	24	100	mV	
	$I_o = 1mA$ to $40mA$		15	50		
Output noise voltage	$f = 10Hz$ to $100 KHz$	25°C		80		
$\mu V$ Dropout voltage V Bias current 6.5				25°C	1.7	mA
				25°C		
		125°C			6	
Bias current change	$V_i = -16V$ to $-27V$	0°C to 125°C			1.5	
	$I_o = 1mA$ to $40mA$				0.1	

\* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\mu F$  capacitor across the input and a  $0.1 \mu F$  capacitor across the output.

\*\* This specification applies only for dc power dissipation permitted by absolute maximum ratings.

## Electrical Characteristics 79L15A

Electrical characteristics at specified virtual junction temperature,  $V_i = -23V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L15A			Units	
		Min	Typ	Max		
Output voltage**		25°C	-14.4	-15	-15.6	V
	$I_o = 1mA$ to $40mA$ , $V_i = -17.5V$ to $-30V$	0°C to 125°C	-14.25		-15.75	
	$I_o = 1mA$ to $70mA$		-14.25		-15.75	
Input regulation	$V_i = -17.5V$ to $-30V$	25°C	65	300	mV	
	$V_i = -20V$ to $-30V$		50	250		
Ripple rejection	$V_i = -18.5V$ to $-28.5V$ , $f = 120Hz$	0°C to 125°C	34	39		dB
Output regulation	$I_o = 1mA$ to $100mA$	25°C	25	150	mV	
	$I_o = 1mA$ to $40mA$		15	75		
Output noise voltage	$f = 10Hz$ to $100 KHz$	25°C		90		$\mu V$
Dropout voltage		25°C		1.7	V	
Bias current		25°C			6.5	mA
		125°C			6	
Bias current change	$V_i = -20V$ to $-30V$	0°C to 125°C			1.5	
	$I_o = 1mA$ to $40mA$				0.1	

## Electrical Characteristics 79L18A

Electrical characteristics at specified virtual junction temperature,  $V_i = -26V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L18A			Units
		Min	Typ	Max	
Output voltage**	25°C	-17.3	-18	-18.7	V
	0°C to 125°C $I_o = 1mA$ to 40mA, $V_i = -20.5V$ to -33V	-17.1		-18.9	
		-17.1		-18.9	
Input regulation	25°C $V_i = -20.5V$ to -33V $V_i = -21V$ to -33V	70	325		mV
		60	275		
Ripple rejection	0°C to 125°C	33	48		dB
Output regulation	25°C $I_o = 1mA$ to 100mA $I_o = 1mA$ to 40mA	27	170		mV
		19	85		
Output noise voltage	25°C	150			μV
Dropout voltage	25°C	1.7			V
Bias current	25°C 125°C		6.5		mA
			6		
Bias current change	0°C to 125°C $V_i = -21V$ to -33V $I_o = 1mA$ to 40mA		1.5		
			0.1		

\* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\mu F$  capacitor across the input and a  $0.1\mu F$  capacitor across the output.

\*\* This specification applies only for dc power dissipation permitted by absolute maximum ratings.

## Electrical Characteristics 79L24A

Electrical characteristics at specified virtual junction temperature,  $V_i = -33V$ ,  $I_o = 40mA$  (unless otherwise noted)

Parameter	Test conditions*	79L24A			Units
		Min	Typ	Max	
Output voltage**	25°C	-23	-24	-25	V
	0°C to 125°C $I_o = 1mA$ to 40mA, $V_i = -27V$ to -38V	-22.8		-25.2	
		-22.8		-25.2	
Input regulation	25°C $V_i = -27V$ to -38V $V_i = -28V$ to -38V	90	350		mV
		75	300		
Ripple rejection	0°C to 125°C	31	47		dB
Output regulation	25°C $I_o = 1mA$ to 100mA $I_o = 1mA$ to 40mA	40	200		mV
		25	100		
Output noise voltage	25°C	200			μV
Dropout voltage	25°C	1.7			V
Bias current	25°C 125°C		6.5		mA
			6		
Bias current change	0°C to 125°C $V_i = -28V$ to -38V $I_o = 1mA$ to 40mA		1.5		
			0.1		

\* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\mu F$  capacitor across the input and a  $0.1\mu F$  capacitor across the output.

\*\* This specification applies only for dc power dissipation permitted by absolute maximum ratings.



**79LXX**

## **Ordering Information**

ORDERING NUMBER	PACKAGE	MARKING
79LXX	TO - 92	ET79LXX

**Address :** 北京市海淀区永定路 88 号长银大厦 6A06--6A07

Rm 6A07,Changyin Office Building ,No.88,Yong Ding Road,Hai Dian District ,Beijing

Postalcode:100039

Tel: 86-010-58895780 / 81 / 82 / 83 / 84      Fax : 010-58895793

[Http://www.estek.com.cn](http://www.estek.com.cn)

Email:sales@estek.com.cn

REV No:01-060806