

A140 - Thermal Grip Glove

Collection: Thermal Protection Gloves

Range: Gloves

Materials: Acrylic, Latex

Inner Pack: 12

Outer Carton: 144

Product information

The Thermal Grip Glove is perfect for construction, transportation, refuse collection, maintenance and local authority work. This glove has a warm acrylic 10 gauge liner and is ideal for more heavy duty, outdoor tasks or those people working in cold conditions.



Thermal Protection Gloves

When cold thermal hazards are present, the hands' motor skills can be greatly reduced, this leads to increased risks of accidents and injury. Specially designed thermal protective gloves are available to combat these hazardous environments.

Gloves

A wide and increasing range of Hand Protection styles is available. In order to help cater to every need. Only the best materials and manufacture methods are used in the production of Portwests' extensive range of Hand Protection products.

Standards

AS/NZS 2161 .5
AS/NZS 2161 .2
AS/NZS 2161 .3
EN 420
EN 388 (1.1.4.2.)
EN 511 (X.1.X.)
ANSI/ISEA 105 - 2011 Cut Level (1)

NO
IMAGE
AVAILABLE

Features

- CE certified
- Specially designed for use in cold conditions
- Crinkle latex grip offers excellent grip
- Palm dipped to increase dexterity and ventilation
- Warm 10 gauge acrylic liner for cold protection
- Retail tag which aids presentation for retail sales

Colours

	Range
Yellow	XS/6 - XXL/11
Black/Black	M/8 - XXL/11
Blue/Black	M/8 - XXL/11
Green/Black	M/8 - XXL/11
Orange	M/8 - XXL/11

PORTWEST[®]

PRODUCT SPECIFICATION & TECHNICAL DATA

A140 - Thermal Grip Glove

Commodity Code: 6116102000

Test House

Cert No: 3021

SATRA (Notified Body No.: 0321)

SATRA Technology Park

NN16 8SD, UK

Cert No: 6776

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
A140B8RM	Blue/Black	45.0	30.0	52.0	0.1000	0.0702	5036108222292	15036108709974
A140B8RL	Blue/Black	45.0	30.0	52.0	0.1200	0.0702	5036108222285	15036108709967
A140B8RXL	Blue/Black	45.0	30.0	52.0	0.1200	0.0702	5036108222308	15036108709981
A140B8RXXL	Blue/Black	45.0	30.0	52.0	0.1400	0.0702	5036108222315	15036108709998