

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking· **1.1 Product identifier**· **Trade name:** Wood Lubricant E-COLL· **Article number:** 4317784305594· **1.2 Relevant identified uses of the substance or mixture and uses advised against**· **Sector of Use**

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

· **Application of the substance / the mixture** Lubricant· **1.3 Details of the supplier of the safety data sheet**· **Manufacturer/Supplier:**

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH

EDE Platz 1

D-42389 Wuppertal

Germany

Tel. +49 202 6096-0

e-mail: sdb@ede.de

· **Further information obtainable from:** Fachbereich Chemisch-Technische-Produkte· **1.4 Emergency telephone number:** Giftinformationszentrum Mainz – Tel.: +49 (6131) 19240**SECTION 2: Hazards identification**· **2.1 Classification of the substance or mixture**· **Classification according to Regulation (EC) No 1272/2008**

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.

· **2.2 Label elements**· **Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

· **Hazard pictograms**

GHS02 GHS09

· **Signal word** Danger· **Hazard statements**

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

(Contd. on page 2)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 1)

H411 Toxic to aquatic life with long lasting effects.

Precautionary statements

- P102 Keep out of reach of children.
- P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
- P211 Do not spray on an open flame or other ignition source.
- P251 Do not pierce or burn, even after use.
- P273 Avoid release to the environment.
- P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
- P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

Additional information:

Buildup of explosive mixtures possible without sufficient ventilation.

2.3 Other hazards

Results of PBT and vPvB assessment










- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

• **Description:** Mixture of substances listed below with nonhazardous additions.

• **Dangerous components:**

EC number: 918-167-1	C9-12-Iso-alkanes  Asp. Tox. 1, H304 Aquatic Chronic 4, H413	25-50%
EC number: 923-037-2 Reg.nr.: 01-2119471991-29	Kohlenwasserstoffe, C10-C12, Isoalkane, <2%Aromaten  Flam. Liq. 3, H226  Asp. Tox. 1, H304  Aquatic Chronic 2, H411	25-50%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32-xxxx	butane, pure  Flam. Gas 1A, H220 Press. Gas (Comp.), H280	10-<25%
CAS: 8042-47-5 EINECS: 232-455-8 Reg.nr.: 01-2119487078-27-xxxx	White mineral oil, petroleum  Asp. Tox. 1, H304	10-<25%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21-xxxx	propane  Flam. Gas 1A, H220  Acute Tox. 1, H330 Press. Gas (Comp.), H280	2.5-10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27-xxxx	isobutane  Flam. Gas 1A, H220 Press. Gas (Comp.), H280	2.5-10%

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 2)

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Personal protection for the First Aider.
- **After inhalation:**
Supply fresh air.
Seek medical treatment in case of complaints.
- **After skin contact:**
Immediately wash with water and soap and rinse thoroughly.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** CO₂, sand, extinguishing powder. Do not use water.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** Can form explosive gas-air mixtures.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Do not inhale explosion gases or combustion gases.
Wear self-contained respiratory protective device.
- **Additional information** Cool endangered receptacles with water spray.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.

(Contd. on page 4)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 3)

Ensure adequate ventilation

· 6.2 Environmental precautions:

Prevent seepage into sewage system, workpits and cellars.
Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

· 6.4 Reference to other sections

See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage**· 7.1 Precautions for safe handling** Use only in well ventilated areas.**· Information about fire - and explosion protection:**

Keep ignition sources away - Do not smoke.

Protect from heat.

Protect against electrostatic charges.

Do not spray onto a naked flame or any incandescent material.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.

· 7.2 Conditions for safe storage, including any incompatibilities**· Storage:****· Requirements to be met by storerooms and receptacles:**

Store in a cool location.

Observe official regulations on storing packagings with pressurised containers.

· Information about storage in one common storage facility: Store away from oxidising agents.**· Further information about storage conditions:** Protect from heat and direct sunlight.**· 7.3 Specific end use(s)** No further relevant information available.**SECTION 8: Exposure controls/personal protection****· 8.1 Control parameters****· Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 4)

· DNELs**CAS: 8042-47-5 White mineral oil, petroleum**

Dermal	Long term value for employees	220 mg/kg bw/Tag (professional use)
Inhalative	Long term value for employees	160 mg/m ³ (professional use)

· Additional information: The lists valid during the making were used as basis.**· 8.2 Exposure controls****· Appropriate engineering controls** No further data; see item 7.**· Individual protection measures, such as personal protective equipment****· General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.

· Hand protection

Protective gloves

· Material of gloves

Nitrile rubber, NBR
Recommended thickness of the material: ≥ 0.4 mm

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye/face protection

Tightly sealed goggles

· Body protection: Protective work clothing**SECTION 9: Physical and chemical properties****· 9.1 Information on basic physical and chemical properties****· General Information**

- | | |
|---|-----------------------------|
| · Colour: | Colourless |
| · Odour: | Characteristic |
| · Odour threshold: | Not determined. |
| · Melting point/freezing point: | Undetermined. |
| · Boiling point or initial boiling point and boiling range | Not applicable, as aerosol. |
| · Flammability | Not applicable. |

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 5)

- **Lower and upper explosion limit**
- **Lower:** 0.6 Vol %
- **Upper:** 8.5 Vol %
- **Flash point:** Not applicable, as aerosol.
- **Ignition temperature:** > 200 °C
- **Decomposition temperature:** Not determined.
- **pH** Not determined.
- **Viscosity:**
- **Kinematic viscosity** Not determined.
- **Kinematic: 23 °C - 4 mm (ISO 2431)**
- **Dynamic:** Not determined.
- **Solubility**
- **water:** Not miscible or difficult to mix.
- **Partition coefficient n-octanol/water (log value)** Not determined.
- **Vapour pressure at 20 °C:** 3500 hPa
- **Density and/or relative density**
- **Density at 20 °C:** 0.7 g/cm³
- **Relative density** Not determined.
- **Vapour density** Not determined.

- **9.2 Other information**
- **Appearance:**
- **Form:** Aerosol
- **Important information on protection of health and environment, and on safety.**
- **Auto-ignition temperature:** Product is not selfigniting.
- **Explosive properties:** Not determined.
- **Solvent separation test:**
- **Organic solvents:** 56.6 %
- **VOC (EC) %** 84,60 %
- **VOC (EC) g/l**
- **VOCV (CH)** 84,60 %
- **Change in condition**
- **Softening point/range**
- **Oxidising properties** Not determined.
- **Evaporation rate** Not applicable.

- **Information with regard to physical hazard classes**
- **Explosives** Void
- **Flammable gases** Void
- **Aerosols**
Extremely flammable aerosol. Pressurised container: May burst if heated.

- **Oxidising gases** Void
- **Gases under pressure** Void
- **Flammable liquids** Void
- **Flammable solids** Void
- **Self-reactive substances and mixtures** Void
- **Pyrophoric liquids** Void
- **Pyrophoric solids** Void
- **Self-heating substances and mixtures** Void
- **Substances and mixtures, which emit flammable gases in contact with water** Void

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 6)

- **Oxidising liquids** Void
- **Oxidising solids** Void
- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

*** SECTION 11: Toxicological information**

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

Kohlenwasserstoffe, C10-C12, Isoalkane, <2%Aromaten

Oral	LD50	>5,000 mg/kg (rat) (OCED 401)
Dermal	LD50	>5,000 mg/kg (rabbit) (OCED 402)

CAS: 106-97-8 butane, pure

Inhalative	LC50/4h	658 ppm (rat)
------------	---------	---------------

CAS: 8042-47-5 White mineral oil, petroleum

Oral	LD50	>5,000 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rabbit)

CAS: 74-98-6 propane

Inhalative	LC50/4h	>20 mg/m ³ (rat)
------------	---------	-----------------------------

- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 7)

- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.

· Aspiration hazard

May be fatal if swallowed and enters airways.

· 11.2 Information on other hazards**· Endocrine disrupting properties**

None of the ingredients is listed.

*** SECTION 12: Ecological information****· 12.1 Toxicity****· Aquatic toxicity:****CAS: 75-28-5 isobutane**

EC50 (48h) 69.43 mg/L (daphnia)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**
Harmful to aquatic organisms
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.

SECTION 13: Disposal considerations**· 13.1 Waste treatment methods:**Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste.
Observe local regulations.

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 8)

· European waste catalogue

16 05 04* gases in pressure containers (including halons) containing hazardous substances

SECTION 14: Transport information**· 14.1 UN number or ID number****· ADR, IMDG, IATA** UN1950**· 14.2 UN proper shipping name****· ADR** UN1950 AEROSOLS
· IMDG AEROSOLS
· IATA Aerosols**· 14.3 Transport hazard class(es)****· ADR****· Class** 2 5F Gases.
· Label 2.1**· IMDG, IATA****· Class** 2 Gases.
· Label 2.1**· 14.4 Packing group****· ADR, IMDG, IATA** Void**· 14.5 Environmental hazards:****· Marine pollutant:** No
· Special marking (ADR): Symbol (fish and tree)**· 14.6 Special precautions for user****· EMS Number:** Warning: Gases.
F-D,S-U**· 14.7 Maritime transport in bulk according to IMO instruments**

Not applicable.

· Transport/Additional information:**· ADR****· Limited quantities (LQ)** 1L
· Transport category 2
· Tunnel restriction code D

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 9)

- **IMDG**
- **Limited quantities (LQ)** 1L
- **UN "Model Regulation":** UN1950, AEROSOLS, 2.1

SECTION 15: Regulatory information

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I Methanol**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3
- **Exposure scenario(s)**
Exposure scenario(s) of ingredients (if present) are available on request at:
sdb@ede.de

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H220 Extremely flammable gas.
H226 Flammable liquid and vapour.
H280 Contains gas under pressure; may explode if heated.
H304 May be fatal if swallowed and enters airways.
H330 Fatal if inhaled.
H411 Toxic to aquatic life with long lasting effects.
H413 May cause long lasting harmful effects to aquatic life.
- **Department issuing SDS:** Product safety department
- **Contact:** sdb@ede.de
- **Date of previous version:** 25.02.2022
- **Version number of previous version:** 304
- **Abbreviations and acronyms:**
ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOCV: Lenkungsabgabe auf flüchtigen organischen Verbindungen, Schweiz (Swiss Ordinance on volatile organic compounds)
VOC: Volatile Organic Compounds (USA, EU)
DNEL: Derived No-Effect Level (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic

(Contd. on page 11)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 25.02.2022

Version number 305 (replaces version 304)

Revision: 25.02.2022

Trade name: Wood Lubricant E-COLL

(Contd. of page 10)

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1A: Flammable gases – Category 1A

Aerosol 1: Aerosols – Category 1

Press. Gas (Comp.): Gases under pressure – Compressed gas

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 1: Acute toxicity – Category 1

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 4: Hazardous to the aquatic environment - long-term aquatic hazard – Category 4

· * Data compared to the previous version altered.

EU