

## SVLC solid carbide boring bar, positive left

For longitudinal and copy turning with VC indexable insert

**ATORN**<sup>®</sup>



### Application

For longitudinal and copy turning with VC indexable insert 55°

### Version

- Precision-manufactured boring bar, **solid carbide**, with internal cooling, type V, attack angle 95°, tip angle 35°, clearance angle 7°

### Advantage

- Slender geometry for longitudinal and copy turning
- Positive geometry for the body ensures low cutting forces

<b>Art. No.</b>	<b>17827 648</b>
<b>ISO name</b>	E 08F SVLC R/L 05
<b>Min. bore diameter</b>	9.2 mm
<b>Shaft diameter</b>	8 mm
<b>Clearance length</b>	26 mm
<b>Length</b>	80 mm
<b>Clamping surface height</b>	7 mm
<b>Programming size</b>	3 mm
<b>Suitable for indexable inserts</b>	VC.. 0501..
<b>Tool design</b>	Left

### EAN-Code

4050293449730