



**Part no.: 50137427**  
**REF 6-S-20x40.P**  
**Reflector**



Figure can vary

## Contents

- Technical data
- Dimensioned drawings

Part no.: 50137427 – REF 6-S-20x40.P – Reflector

## Technical data

### Basic data

Area of application	Pharmaceutical
---------------------	----------------

### Mechanical data

Design	Rectangular
Mounting dimension, width	20 mm
Reflection surface width	16 mm
Mounting dimension, height	60 mm
Reflection surface height	38 mm
Mounting dimension, thickness	6 mm
Direction independent	No
Triple reflector size	0.3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PET
Structure, active surface	Mikrotriple
Net weight	6 g
Type of fastening	Screw type
Compatibility of materials	Alcohol ECOLAB H2O2

### Environmental data

Ambient temperature, operation	-40 ... 70 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

