



LARGE INSULATION CRIMP

MATERIAL NUMBER	FINISH	HOLE
43178-2001	999	NOT USED
43178-2002	H901	NOT USED
43178-2003	F542	NOT USED

- NOTES**
- MATERIAL: BRASS
 - FINISH:
999 - UNPLATED
H901 - 20 MICROINCH MIN. HOT TIN DIP
F542 - 15 MICROINCH MIN. SELECT GOLD IN CONTACT AREA,
50 MICROINCH TIN-LEAD IN CRIMP AREA,
NICKEL UNDERPLATE OVERALL.
 - PRODUCT SPECIFICATION : PS-44441-001
 - TERMINAL FOR USE WITH
A. SINGLE 14-16 AWG. UL 1007 OR 1015 STYLE WIRE, OR
B. DOUBLE 18-20 AWG. UL 1015 STYLE WIRE (STACKED VERTICALLY)

REVISE NOTE #4 IEC NO. UCP2010-2241 DRAWN BY: DRWNAELHAG 20/00/03/03 CHKD: JRELL 20/00/03/03 APPR: FSWITH 20/00/03/17	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION															
	$\nabla=0$ $\nabla=0$ $\nabla=0$	<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>±.010</td> <td>±.010</td> </tr> <tr> <td>3 PLACES</td> <td>±.025</td> <td>±.014</td> </tr> <tr> <td>2 PLACES</td> <td>±.035</td> <td>±.014</td> </tr> <tr> <td>1 PLACE</td> <td>±.035</td> <td>±.014</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	±.010	±.010	3 PLACES	±.025	±.014	2 PLACES	±.035	±.014	1 PLACE	±.035	±.014	IN/MM	8:1	INCH	
		mm	INCH																		
	4 PLACES	±.010	±.010																		
3 PLACES	±.025	±.014																			
2 PLACES	±.035	±.014																			
1 PLACE	±.035	±.014																			
DATE: 1995/06/19	DATE: 1995/06/19	DATE: 1995/06/19	DATE: 1995/06/19	TERMINAL, CRIMP MALE TAB .125/(3.18)X.020/(0.51) SABRE - F.B.S. - TPA																	
MATERIAL NO. SEE CHART DOCUMENT NO. SD-43178-2***	MOLEX INCORPORATED SHEET NO. 1 OF 1																				