



MOLDED CASE CIRC.BREAKER 3RV1 FOR MOTOR PROTECTION STANDARD SWITCHING CAPACITY RATED CURRENT IN=100A ELECTRONIC RELEASE SHORT-CIRCUIT PROTECTION ADJUSTABLE 6-13XLN OVERLOAD PROTECTION UEL 0.4-1XLN, CLASS 10A-30 ICU =120KA AT 400V 3-POLE, SCREW TERMINAL INCL.PHASE BARRIERS

product brand name		SIRIUS
Product designation		molded-case circuit breaker
Design of the product		for motor protection

General technical data:

Shock resistance		12g / 11 ms
Surge voltage resistance Rated value	V	8 000
Mechanical service life (switching cycles)		
• of the main contacts typical		20 000
Protection class IP		
• on the front		IP20
Equipment marking		
• acc. to DIN EN 61346-2		Q

Main circuit:

Number of poles for main current circuit		3
Adjustable response value current of the current-dependent overload release	A	40 ... 100
Operating voltage		
• Rated value	V	690
• at AC-3 Rated value maximum	V	690
Operating current		
• at AC-3		
— at 400 V Rated value	A	250
Operating power		
• at AC-3		
— at 400 V Rated value	kW	55

Operating frequency • at AC-3 maximum	1/h	15
Auxiliary circuit:		
Number of CO contacts • for auxiliary contacts		0
Product expansion Auxiliary switch		Yes
Protective and monitoring functions:		
Trip class		CLASS 10, 20 and 30 adjustable
Maximum short-circuit current breaking capacity (Icu) • with AC at 240 V Rated value • with AC at 400 V Rated value • with AC at 500 V Rated value • with AC at 690 V Rated value	kA kA kA kA	100 120 85 70
Short-circuit:		
Design of the overcurrent release and short-circuit release		electronic
Installation/ mounting/ dimensions:		
mounting position		any
Mounting type		screw fixing
Height	mm	205
Width	mm	105
Depth	mm	103.5
Required spacing • with side-by-side mounting — Backwards — at the side	mm mm	0 0
Connections/ Terminals:		
Type of electrical connection • for main current circuit • for auxiliary and control current circuit		screw-type terminals screw-type terminals
Arrangement of electrical connectors for main current circuit		front side
Product function • removable terminal for auxiliary and control circuit		No
Safety related data:		
Protection against electrical shock		finger-safe
Mechanical data:		
Size of the circuit-breaker		3RV1.6
Ambient conditions:		

Installation altitude at height above sea level maximum	m	2 000
Ambient temperature		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +70
• during transport	°C	-40 ... +70

Certificates/ approvals:

General Product Approval	Test Certificates	Shipping Approval
--------------------------	-------------------	-------------------



[Special Test Certificate](#)



GL

Shipping Approval	other
-------------------	-------



LRS



RINA



RMRS

[Confirmation](#)

[Declaration of Conformity](#)

[Environmental Confirmations](#)

other



VDE

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV10637AL10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<http://support.automation.siemens.com/WW/view/en/3RV10637AL10/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV10637AL10&lang=en



last modified:



11.03.2015