



PLUG-IN RELAY COMPLETE UNIT DC 24V, 4 CO CONTACT LED MODULE RED STANDARD PLUG-IN SOCKET SCREW TERMINAL 3.5 MM PINNING

Figure similar

General technical data:		
Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> <li>• for DC Rated value</li> <li>— minimum</li> <li>— maximum</li> </ul>	V	24
	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		4
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> <li>• at DC-13</li> <li>— at 24 V</li> <li>• at AC-15</li> <li>— at 230 V</li> </ul>	A	6
	A	4
Design of the switching function positively driven		No
Switching behavior		monostable
Mechanical data:		
Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	28
Height	mm	72
Depth	mm	74
Certificates/ approvals:		



[Declaration of Conformity](#)

#### Further information

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZS:PT5A5L24>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT5A5L24>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=LZS:PT5A5L24&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZS:PT5A5L24&lang=en)

last modified:

15.01.2015