

Product type designation



RF640T transponder

SIMATIC RF640T TOOL-TAG; 50 X 8 MM (DXH); ON METAL
 TRANSPONDER ISO 18000-6C, EPC CLASS 1 GEN 2
 FREQUENCY 902 UP TO 928 MHZ (FCC) CHIP TYPE, NXP G2XM
 EPC 240 BIT 64 BYTE ADD-ON MEMORY -25 UP TO +85 DGR/C;
 MINIMAL ORDER QUANTITY 10 PCS

Wireless frequencies	
Operating frequency	902 ... 928 MHz
Electrical data	
Range / maximum	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
Protocol / with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate / with radio transmission / maximum	320 kbit/s
Product property / multitag-capable	Yes
Polarization	Linear
Product component / Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity / of the user memory	64 byte
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles / at ambient temperature < 40 °C / maximum	100000000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	100000
Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	lock, unlock, write protection, password protection
Type of transponder chip used	NXP G2XM

Mechanical data	
Material	PA12
Color	anthracite
Tightening torque / of the screw for securing the equipment / maximum	1.2 N·m
Mounting distance / relating to metal surfaces / recommended / minimum	0 mm

Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during read/write access 	-25 ... +85 °C
<ul style="list-style-type: none"> outside the read/write area 	-40 ... +125 °C
<ul style="list-style-type: none"> during storage 	-40 ... +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1000 m/s ²
Resistance against vibration	200 m/s ²

Design, dimensions and weight	
Height	8 mm
Diameter	50 mm
Net weight	13 g
Mounting type	2 x M4 screws

Product properties, functions, components / general	
Product property	
<ul style="list-style-type: none"> silicon-free 	Yes
<ul style="list-style-type: none"> printable 	No

Standards, specifications, approvals	
MTBF	1757 y

Further Information / Internet Links	
Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/automation/net/catalog
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	09.03.2015