

Product type designation

Product description

Fiber optic standard cable

Flexible glass fiber-optic cable, preferred length, preassembled SIMATIC NET, FIBER OPTIC CABLE (62.5/125)STANDARD CABLE, SPLITTABLE, PREASSEMBLED WITH 4 BFOC CONNECTORS, LENGTH: 30 M



Suitability for use	Cable for installation indoors and outdoors
Version of the assembled FO cable	Assembled with four BFOC connectors
Cable designation	AT-V(ZN)YY 2X1 G 62.5/125
Cable length	30 m

Optical data

Damping ratio per length	
<ul style="list-style-type: none"> • at 850 nm / maximum • at 1300 nm / maximum 	<p>3.1 dB/km</p> <p>0.8 dB/km</p>
Bandwidth length product	
<ul style="list-style-type: none"> • at 850 nm • at 1300 nm 	<p>200 GHz·m</p> <p>600 GHz·m</p>

Mechanical data

Number of fibers / per FOC core	1
Number of FO cores / per FOC cable	2
Version of the FO conductor fiber	Multimode graded-index fiber 62.5/125 μm, OM 1
Design of the FOC core	Compact core, diameter 900 μm
Design of the fiber-optic cable	Segmentable outer conductor
Outer diameter	
<ul style="list-style-type: none"> • of the optical fibers • of the optical fiber sheath • of the FOC core sheath 	<p>62.5 μm</p> <p>125 μm</p> <p>3.5 mm</p>
Width / of cable sheath	9.8 mm
Thickness / of cable sheath	6.3 mm

Material	
<ul style="list-style-type: none"> • of the fiber-optic cable core • of the optical fiber sheath • of the FOC core sheath • of the fiber-optic cable sheath • of the strain relief 	Quartz glass Quartz glass PVC PVC Aramid fibers and glass roving
Color	
<ul style="list-style-type: none"> • of the FOC core sheath • of cable sheath 	Gray Black
Bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	80 mm 80 mm
Tensile load / during operation / maximum	1500 N
Continuous lateral force per length	150 N/cm
Weight per length	70 kg/km

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C -5 ... +50 °C
Burning behavior	Flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
Chemical resistance	
<ul style="list-style-type: none"> • to mineral oil • to grease 	not resistant not resistant
Radiological resistance / to UV radiation	resistant
Protection class IP	IP20

Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> • halogen-free • silicon-free 	No Yes
Product component / Rodent protection	No
Cable length	
<ul style="list-style-type: none"> • for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum • for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum • for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum • for glass FOC / with PROFIBUS / maximum 	4000 m 350 m 550 m 3000 m

Standards, specifications, approvals

Certificate of suitability

- RoHS conformity

Yes

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015