

Twist drill set in box, type N HSS, steam-treated

for universal use up to 1000 N/mm²

ATORN[®]

Application

Proven standard geometry for universal use in the material groups of steel, non-ferrous metals and cast metal up to a strength of 1000 N/mm².

Version

- Twist drill with universal standard geometry

Advantage

- long-term proven cutting geometry: excellent all-round properties and precise cutting behaviour
- universal use up to 1000 N/mm²
- steam treatment ensures good adhesion to the drill and increases the service life
- Robust and user-friendly plastic box ensures reliable protection and good accessibility



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20		10		40	60	70	45	40	30	20	10	25					

Art. No.	11042 051
Composition of set	1,0-10,0
Pitch of drill diameter	0.5 mm
Number of pieces in assortment/set	19 PCS
Surface	Vaporised
Cutting material	HSS
Type	N (no. 11020)
DIN	338

EAN-Code

4050293027761