

## Short-length chucks

ERICKSON system with straight shank

**ORION**<sup>®</sup>

### Application:

For use on NC and CNC machining equipment.

### Execution:

- Min. tensile strength at core 800 N/mm.
- Hardened.
- Clamping of drill bits on drill heel possible.
- With adjustable longitudinal stop.
- Collets no. 23326.

### Advantage:

- With straight shank - extremely slim version.
- Very good accessibility in confined spaces.

### Delivery:

1x ERICKSON short chuck system with cylindrical shank.



<b>Art. no.</b>	<b>23325 300</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23325300
<b>Collet type</b>	DK 30
<b>Shank diameter</b>	12 mm
<b>Min./max. clamping width</b>	1-6.5 mm
<b>Width across flats</b>	13 mm
<b>Outer diameter</b>	14 mm
<b>Shaft length</b>	76 mm
<b>Length of head</b>	36 mm
<b>Min. clamp in depth</b>	38 mm
<b>Max. clamp in depth</b>	99 mm
<b>Gross Weight</b>	0.085 kg
<b>Product Group</b>	218

### EAN

4039247 156979