

## ERGO stair climber and electric lift

Load-bearing capacity 170 kg

**DMS**<sup>®</sup>  
ARBEIT WIRD LEICHTER

### Application:

Ideal for vertical transport and lifting over stairs

### Execution:

- Lithium-ion battery.
- Height-adjustable handle
- Lift lifting height 1000 mm
- Battery capacity 1200 - 1700 steps/charge
- Charging voltage 110-240 V AC
- Slow climbing speed 17 steps/minute
- Fast climbing speed 34 steps/minute
- Lift speed: 30 sec.



<b>Art. no.</b>	<b>50191 104</b>
<b>Brand</b>	DMS
<b>Manufacturer Part Number</b>	SCL170
<b>Lift height</b>	1000 mm
<b>Height</b>	1390 mm
<b>Toe plate width</b>	430 mm
<b>Charging voltage</b>	240 V
<b>Toe plate depth</b>	290
<b>Material</b>	Aluminium
<b>Material of wheel</b>	Solid rubber
<b>Charging time</b>	2.5 h
<b>Load-carrying capacity</b>	170 kg
<b>Power rating</b>	400 W
<b>Width</b>	650 mm
<b>Weight of rechargeable battery/battery</b>	3.1 kg
<b>Rechargeable battery/battery capacity</b>	10 Ah
<b>Depth</b>	585 mm
<b>Battery voltage</b>	48 V
<b>Battery included</b>	Yes
<b>Gross Weight</b>	34.000 kg
<b>Product Group</b>	586

### EAN

4260625310434