

## Drill/counter sink milling cutter, 90°, with Weldon shank

For AP... indexable milling inserts T003..

**ATORN®**

### Application


For drilling/countersinking in all materials.

### Version

- With Weldon shank
- Wear-resistant, nickel-plated version
- Robust supports
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm

### Advantage

- High cutting performance
- Safe chip removal thanks to positive cutting geometry



|                                      |                  |
|--------------------------------------|------------------|
| <b>Art. No.</b>                      | <b>16017 051</b> |
| <b>Cutting edge diameter</b>         | 20 mm            |
| <b>Clearance length</b>              | 30 mm            |
| <b>Length</b>                        | 150 mm           |
| <b>Shaft diameter</b>                | 20 mm            |
| <b>max. ap</b>                       | 17 mm            |
| <b>Number of cutting edges</b>       | 2 PCS            |
| <b>Number of cutting inserts</b>     | 3 PCS            |
| <b>Suitable indexable insert no.</b> | 21               |

### EAN-Code

4050293113358

