

## Electrically operated drum pump HORNET W 85

Completely ready for use with suction pipe, pressure hose and tap valve



### Application:

For pumping heating and diesel oils of hazard class A III from all standard containers. Fast and simple filling of heating oil into transport containers and refuelling of all kinds of diesel vehicles.

### Execution:

- 230-V voltage, 50/60 Hz, shockproof, noise-suppressed
- Self-priming hybrid pump
- Suction hose with filter
- Delivery hose with automatic nozzle valve and hose swivel joint
- 4-m connection cable with plug
- Pump housing and nozzle valve made from high-quality, impact-resistant plastic



<b>Art. no.</b>	<b>56345 140</b>
<b>Brand</b>	HORN TECALEMIT
<b>Manufacturer Part Number</b>	108500100
<b>Model</b>	HORNET W 85
<b>Max. immersion depth</b>	1600 mm
<b>Feed quantity</b>	85 l/min
<b>Suitable for container</b>	60-200 litres
<b>Gross Weight</b>	9.600 kg
<b>Product Group</b>	575

### EAN

4031109002677