SIEMENS

Data sheet

3RM1002-2AA04



Direct starter, 3RM1, 500 V, 0.09 - 0.75 kW, 0.4 - 2 A, 24 V DC, spring-type terminals

product brand name	SIRIUS			
product brand name	Motor starter			
product designation	Direct-on-line starter			
design of the product				
product type designation	with electronic overload protection 3RM1			
General technical data				
trip class	CLASS 10A			
equipment variant according to IEC 60947-4-2	3			
product function	Direct-on-line starter			
intrinsic device protection	Yes			
for power supply reverse polarity protection	No Yes			
suitability for operation device connector 3ZY12	500 V			
insulation voltage rated value				
overvoltage category				
surge voltage resistance rated value	6 kV			
maximum permissible voltage for safe isolation	500.1/			
between main and auxiliary circuit	500 V			
between control and auxiliary circuit	250 V			
shock resistance	6g / 11 ms			
vibration resistance	1 6 Hz, 15 mm; 20 m/s², 500 Hz			
operating frequency maximum	1 1/s			
mechanical service life (switching cycles) typical	30 000 000			
reference code according to IEC 81346-2	Q			
Substance Prohibitance (Date)	03/01/2017			
product function	No.			
direct start	Yes			
reverse starting	No			
product function short circuit protection	No			
Electromagnetic compatibility				
EMC emitted interference according to IEC 60947-1	class A			
EMC immunity according to IEC 60947-1	Class A			
conducted interference				
 due to burst according to IEC 61000-4-4 	3 kV / 5 kHz			
 due to conductor-earth surge according to IEC 61000-4-5 	2 kV			
 due to conductor-conductor surge according to IEC 61000-4-5 	1 kV			
 due to high-frequency radiation according to IEC 61000-4-6 	10 V			
field-based interference according to IEC 61000-4-3	10 V/m			


electrostatic discharge according to IEC 61000-4-2	4 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to CISPR11	Class B for the domestic, business and commercial environments
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments
Safety related data	
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe
Main circuit	5
number of poles for main current circuit	3
design of the switching contact	Hybrid
design of the switching contact as NO contact for signaling function	OUT, electronic, 24 V DC, 15 mA
adjustable current response value current of the current-dependent overload release	0.4 2 A
minimum load [%]	20 %; from set rated current
type of the motor protection	solid-state
operating voltage rated value	48 500 V
relative symmetrical tolerance of the operating voltage	10 %
operating frequency 1 rated value	50 Hz
operating frequency 2 rated value	60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operational current	
• at AC at 400 V rated value	2 A
 at AC-3 at 400 V rated value 	2 A
 at AC-53a at 400 V at ambient temperature 40 °C 	2 A
rated value	
ampacity when starting maximum	16 A
operating power for 3-phase motors at 400 V at 50 Hz	0.09 0.75 kW
Inputs/ Outputs	
input voltage at digital input	
 at DC rated value 	24 V
 with signal <0> at DC 	0 5 V
● for signal <1> at DC	15 30
input current at digital input	
• for signal <1> at DC	11 mA
• with signal <0> at DC	1 mA
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15 at 230 V maximum	3 A
operational current of auxiliary contacts at DC-13 at 24 V maximum	1 A
Control circuit/ Control	
type of voltage of the control supply voltage	DC
control supply voltage at DC rated value	
	19.2 30 V
relative negative tolerance of the control supply voltage at DC	20 %
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC	
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply	20 %
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC	20 % 25 %
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated	20 % 25 %
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC	20 % 25 % 24 V
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC • initial value • full-scale value control current at DC	20 % 25 % 24 V 0.8
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC • initial value • full-scale value control current at DC • in standby mode of operation	20 % 25 % 24 V 0.8
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC • initial value • full-scale value control current at DC • in standby mode of operation • when switching on	20 % 25 % 24 V 0.8 1.25
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC • initial value • full-scale value control current at DC • in standby mode of operation • when switching on • during operation	20 % 25 % 24 V 0.8 1.25 25 mA 150 mA 70 mA
relative negative tolerance of the control supply voltage at DC relative positive tolerance of the control supply voltage at DC control supply voltage 1 at DC rated value operating range factor control supply voltage rated value at DC • initial value • full-scale value control current at DC • in standby mode of operation • when switching on	20 % 25 % 24 V 0.8 1.25 25 mA 150 mA


e in switching state OFF				
 in switching state OFF — with bypass circuit 	0.6 W			
in switching state ON	0.0 11			
- with bypass circuit	1.68 W			
Response times	1.00 W			
ON-delay time	60 90 ms			
OFF-delay time	60 90 ms			
Power Electronics	00 00 m3			
operational current				
• at 40 °C rated value	2 A			
• at 50 °C rated value	2 A			
• at 55 °C rated value	2 A			
at 60 °C rated value	2 A			
Installation/ mounting/ dimensions				
mounting position	vertical, horizontal, standing (observe derating)			
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail			
height	100 mm			
width	22.5 mm			
depth	141.6 mm			
required spacing				
with side-by-side mounting				
— forwards	0 mm			
— backwards	0 mm			
— upwards	50 mm			
— downwards	50 mm			
— at the side	0 mm			
 for grounded parts 				
— forwards	0 mm			
— backwards	0 mm			
— upwards	50 mm			
— at the side	3.5 mm			
— downwards	50 mm			
Ambient conditions				
installation altitude at height above sea level maximum	4 000 m; For derating see manual			
ambient temperature				
during operation	-25 +60 °C -40 +70 °C			
during storage	-40 +70 °C			
• during transport environmental category during operation according to IEC	3K6 (no ice formation, only occasional condensation), 3C3 (no salt			
60721	mist), 3S2 (sand must not get into the devices), 3M6			
relative humidity during operation	10 95 %			
air pressure according to SN 31205	900 1 060 hPa			
Communication/ Protocol				
protocol is supported				
PROFINET IO protocol	No			
PROFIsafe protocol	No			
product function bus communication	No			
protocol is supported AS-Interface protocol	No			
Connections/ Terminals				
type of electrical connection	spring-loaded terminals (push-in) for main circuit, spring-loaded terminals (push-in) for control circuit			
 for main current circuit 	spring-loaded terminals (push-in)			
for auxiliary and control circuit	spring-loaded terminals (push-in)			
wire length for motor unshielded maximum	100 m			
type of connectable conductor cross-sections				
for main contacts				
— solid	1x (0.5 4 mm ²)			
 finely stranded with core end processing 	1x (0.5 2.5 mm²)			
 finely stranded without core end processing at AWG cables for main contacts 	1x (0.5 4 mm²) 1x (20 12)			

connectable condu contacts	ctor cross-section for	main					
 solid or strand 	 solid or stranded 			mm²			
 finely stranded 	0.5 2.	.5 mm²					
 finely stranded 	 finely stranded without core end processing 						
connectable conductor cross-section for auxiliary contacts		0.5 4 mm²					
solid or stranded			0.5 1.5 mm²				
 finely stranded with core end processing 		0.5 1 mm²					
 finely stranded 	 finely stranded without core end processing 			0.5 1.5 mm²			
type of connectable conductor cross-sections							
 for auxiliary co 	ontacts						
— solid			1x (0.5 .	1.5 mm²), 2x (0.5	5 1.5 mm²)		
— finely stra	anded with core end proc	essing	1x (0,5 .	1,0 mm²), 2x (0,5	5 1,0 mm²)		
— finely stra	anded without core end p	rocessing		1.5 mm²), 2x (0.5			
-	s for auxiliary contacts	-		16), 2x (20 16)			
AWG number as coded connectable conductor cross section							
for main contacts			20 12				
 for auxiliary co 	 for auxiliary contacts 			20 16			
UL/CSA ratings							
yielded mechanical	performance [hp]						
 for single-phase 							
— at 230 V rated value		0.125 hp					
• for 3-phase AC motor							
— at 200/208 V rated value		0.333 hp					
— at 220/230 V rated value		0.333 hp					
- at 460/480 V rated value		0.75 hp					
	operating voltage at AC						
 according to U 			480 V				
according to CSA rated value		400 V					
Certificates/ approva							
General Product A						EMC	
General Floudet A	ppioval					LINC	
	<u>Confirmation</u>	(CC)	(UL) III	EHC	RCM	
Declaration of Conformity	Test Certificates	other	F	Railway			
CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	<u>Confirmatic</u>	on Si	pecial Test Certific- ate			


Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RM1002-2AA04 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM1002-2AA04 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RM1002-2AA04 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RM1002-2AA04&lang=en





Subject to change without notice © Copyright Siemens



last modified:

11/3/2021 🖸