





Part no.: 50130289
TK 50 x100-Set
Reflector

Figure can vary

Contents

- Set consists of
- Technical data
- Dimensioned drawings

Set consists of

	Quantity	Part no.	Designation	Article	Description
	2	50009419	BT 910M	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Metal
	1	50003191	TK 50x100	Reflector	Design: Rectangular Reflective surface: 46 mm x 96 mm Triple reflector size: 4 mm Material: Plastic Base material: Plastic Chemical designation of the material: PMMA8N Fastening: Adhesive

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	49.5 mm
Reflection surface width	46 mm
Mounting dimension, height	99 mm
Reflection surface height	96 mm
Mounting dimension, thickness	9 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	32 g
Type of fastening	Adhesive

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

