



- O IP68 rated
- IP69K, Tested in accordance with DIN 40050/Part 9 IP6k9k
- Cat 5e or Cat 6a compliant
- O PUR / PVC jacket on cable
- O Shielded system
- O Cat 5e or Cat 6a shielded coupler
- O Shroud on RJ45
- Screw coupling
- Rewireable flex connector
- O PCB mounted panel connector
- O IDC termination panel connector
- O Earth lead version of panel adaptor
- EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1

- O Dust and waterproof sealing when mated
- O Data rate up to 100MHz
- O Good chemical resistance, flame retardant
- O High noise immunity and EMI protection
- Maintains shielding
- O Protection from abuse and mis-mating
- O Secure, proven locking system
- Ability to 'field' terminate
- Direct PCB mount panel connector
- Simple termination
- Continuous screening of panel mount connector

#### BUCCANEER FOR DATA


## Standard Buccaneer - Ethernet



Patch Cord Flex Connector - PUR Jacket




- Mates with all panel mounting connectors
- Patchcords with IP68 connector
- Supplied with shielded RJ45 plug
- Single or double end terminated
- O Standard lengths: 2m, 3m & 5m
- S-FTP cable construction
- PUR / PVC jacket cable
- Wiring configuration to 568-B



PX0836

Don't are	<b>T</b>	Lamente	Describetion
Part no.	Туре	Length	Description
PX0836/2M00	Wire end	2m	Cat 5e IP68 RJ45 Buccaneer to bare end
PX0836/3M00	Wire end	3m	Cat 5e IP68 RJ45 Buccaneer to bare end
PX0836/5M00	Wire end	5m	Cat 5e IP68 RJ45 Buccaneer to bare end
PX0837/2M00	Single ended	2m	Cat 5e IP68 RJ45 Buccaneer to Shielded RJ45
PX0837/3M00	Single ended	3m	Cat 5e IP68 RJ45 Buccaneer to Shielded RJ45
PX0837/5M00	Single ended	5m	Cat 5e IP68 RJ45 Buccaneer to Shielded RJ45
PX0838/2M00	Double ended	2m	Cat 5e IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0838/3M00	Double ended	3m	Cat 5e IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0838/5M00	Double ended	5m	Cat 5e IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0896/2M00	Wire end	2m	Cat 6a IP68 RJ45 Buccaneer to bare end
PX0896/3M00	Wire end	3m	Cat 6a IP68 RJ45 Buccaneer to bare end
PX0896/5M00	Wire end	5m	Cat 6a IP68 RJ45 Buccaneer to bare end
PX0897/2M00	Single ended	2m	Cat 6a IP68 RJ45 Buccaneer to Shielded RJ45
PX0897/3M00	Single ended	3m	Cat 6a IP68 RJ45 Buccaneer to Shielded RJ45
PX0897/5M00	Single ended	5m	Cat 6a IP68 RJ45 Buccaneer to Shielded RJ45
PX0898/2M00	Double ended	2m	Cat 6a IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0898/3M00	Double ended	3m	Cat 6a IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer
PX0898/5M00	Double ended	5m	Cat 6a IP68 RJ45 Buccaneer to IP68 RJ45 Buccaneer




Re wireable Flex Connector



PX0834

- Mates with all panel mounting connectors
- Supplied with shielded RJ45 plug
- Two versions:
  PUR / PVC jacket cable (Cat 5e / 6a)
  for other cable sizes from
  3.5 to 8mm dia.




#### Part no. Description

PX0834/A Cat 5e Cable glands optimised for PUR jacket cable to maintain Cat 5e performance
PX0834/B Cat 5e Suitable for use with cables from 3.5 to 8mm diameter
PX0894/A Cat 6a Cable glands optimised for PVC jacket cable to maintain Cat 6a performance
PX0894/B Cat 6a Suitable for use with cables from 3.5 to 8mm diameter

Panel Mounting Connector



- O Cat 5e mates with PX0836, PX0837, PX0838 & PX0834 flex connectors
- Cat 6a mates with PX0896, PX0897, PX0898 & PX0894 flex connectors
- Standard RJ45 patchcord can be plugged into rear
- O Version with earth wire available
- Single hole fixing
- Complete with panel sealing gasket



PX0833


Part no.	Description	Fixing
PX0833	Cat 5e coupler	Front panel mounted
PX0833/E	Cat 5e coupler + earth wire	Front panel mounted
PX0893	Cat 6a coupler	Front panel mounted
PX0893/E	Cat 6a coupler + earth wire	Front panel mounted



Flanged Mounting Connector



- Ocat 5e mates with PX0836, PX0837, PX0838 & PX0834 flex connectors
- Cat 6a mates with PX0896, PX0897, PX0898 & PX0894 flex connectors
- Standard RJ45 patchcord can be plugged into rear
- Version with earth wire available
- Flange fixing
- Complete with panel sealing gasket



PX0870


Part no.	Description	Fixing
PX0870 PX0870/E PX0890 PX0890/E	Cat 5e coupler Cat 5e coupler + earth wire Cat 6a coupler Cat 6a coupler + earth wire	Flange mounting Flange mounting Flange mounting Flange mounting

PCB Mounting Connector



PX0839/PC

- O Cat 5e shielded RJ45 interface
- Rear of panel mounted
- Mates with PX0836, PX0837,
- PX0838 and PX0834 flex connectors
- O For direct vertical mounting to
- O PCB, straight pins
- Complete with panel sealing
- O PX0839/PC gasket



Part no. Description Fixing


PX0839/PC Cat 5e connector - PC Rear panel mounted

PCB Mounting Connector



PX0839/90

- O Cat 5e shielded RJ45 interface
- Rear of panel mounted
- Mates with PX0836, PX0837,
- O PX0838 and PX0834 flex connectors
- For direct horizontal mounting to PCB, 90° pins
- Complete with panel sealing PX0839/90 gasket



FED Octor's TYPE 233

Part no.	Description	Fixing
PX0839/90	Cat 5e connector - PC	Rear panel mounted




Panel Mounting Connector



PX0839/IDC

- O Cat 5e shielded RJ45 interface
- O Rear of panel mounted
- Mates with PX0836, PX0837,
- O PX0838 and PX0834 flex connectors
- Two IDC blocks for discrete termination
- O Complete with panel sealing



Part no. Description Fixing

PX0839/IDC Cat 5e coupler


Rear panel mounted

Shield Back Shell Accessory



PX0888

- Maintains RJ45 coupler screening directly to panel
- Shielding can is fixed to rear of panel mount connector
- O For use on PX0833



Part no. Description


PX0888 Shielding backshell accessory

Accessories



Sealing Caps

- Sealing caps to maintain IP68 rating when connectors are not in use
- Replacement shielded RJ45s
- Hand crimp tool for shielded RJ45
- Patch cord cable available in 50m reels



## Part no. Description

PX0835 PX0733	Sealing Cap for flex connectors (PX0834, PX0836-838, PX0894, PX0896-898) Sealing Cap for panel mounting connector (PX0833, PX0870, PX0893, PX0890)
PX0711	Sealing Cap for rear panel mounting connector (PX0839)
14151	Cat 5e & Cat 6a Hand crimp tooling + die set
14199	Cat 5e PUR Jacket Cable - 50m reel
14150	Cat 5e Replacement shielded RJ45
15241	Cat 6a PVC Jacket Cable - 50m reel



#### **Connectors**

Sealing IP69K, Tested in accordance with

DIN 40050/Part 9 IP6k9k

IP68, EN60529:1992+A2:2013

(10m depth for 2 weeks)

Operating Temperature –20°C to +70°C

Materials - Overmoulded

Overmould material PVC (black) Flammability rating UL94V-0

Salt Mist EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1

#### **Materials - Re-wireable and Panel Connectors**

Connector body & locking ring
Panel connector
Panel connector
Flammability rating
'O' rings
Panel Gasket - round
Panel Gasket - flange
RoHS
Polyester
Nylon 6
UL94V-0
Silicone
Silicone
Panel Gasket - Round
Compliant

Cables	Cat 5e	Cat 6a
Conductors	24AWG (7/0.2mm) bare copper	26AWG (7/0.16mm) bare copper
Insulation	HD-PE	PE (Skin - Foam - Skin)
Pair	2 of the above cores twisted	2 of the above cores twisted
Core	4 of the above cores	4 of the above cores
Screen	1 layer mylar and aluminium tape,	Aluminium & Polyester
Braid	0.12mm tinned copper braid	Tinned Copper Braid
Sheath	PUR Jacket Black	PVC Jacket Black
Op Temperature	–25°C to +85°C	–25°C to +75°C
Diameter	6.1mm nominal	6.0 mm nominal
Flame Test		FT4
Electrical @ 20°C		
Characteristic:		
Impedance	$100 \Omega \pm 15 \Omega$ @ $100 MHz$	
Capacitance	330pF/km	
Conductor Loop		
Resistance	29/Ω100m maximum	26Ω /km
Skew	45 nsec/100m @ 100MHz	
TIA/EIA Rating	Cat 5e	Cat 6A
Mechanical Characteristics		
Minimum Tensile Strength of Jacket (kgf/mm²)		1.05
Maximum Length for Strip of Jacket (mm)		40

#### Cable construction - PX0836, PX0837, PX0838 and 14199

24 AWG
7/0.20mm conductor

Braiding
7/0.12mm

Jacket
6.10mm dia

Mylar Tape
Insulation - HD - PE
Aluminium/ PEPT tape
Drain Wire

Polyurethane (PUR) Jacket

#### Cable construction - PX0896, PX0897, PX0898 and 15241



Polyvinyl Chloride (PVC) Jacket

# BUCCANEER FOR DATA Standard Buccaneer - Ethernet



RJ45 Plug	Cat 5e & POE	Cat 6a
Materials Moulding Flammability Contact material Contact plating Operating Temperature Mating cycles RoHS	Polycarbonate UL94V-0 Phosphor Bronze 50 micron gold -40°C to +70°C 1,000 cycles Compliant	Polycarbonate UL94V-0 Phosphor Bronze 50 micron gold -40°C to +70°C 1,000 cycles Compliant
<b>Electrical</b> No. Conductors Conductor types	8 24-28AWG, solid or multistranded	8 24-28AWG, solid or multistranded
Current rating Voltage rating Contact resistance Performance	350mA 37V ac, 57V dc 10mΩ max. Cat 5e & POE	1.5 A 30V ac, 42V dc 10mΩ max. Cat 6a
RJ45 Coupler	Cat 5e	Cat 6a
Materials Coupler Shell Coupler Plating Moulding Flammability Contact material Contact plating Operating Temperature Mating cycles RoHS	Copper Alloy Nickel ABS UL94V-0 Phosphor Bronze 50 micron gold -40°C to +70°C 1,000 cycles Compliant	Copper Alloy Nickel ABS UL94V-0 Phosphor Bronze 50 micron gold 0°C to +70°C 1,000 cycles Compliant
Electrical No. Conductors Current rating	8 1.5A	8 1.5A

30V ac, 42V dc

10mV max.

Cat 5e

30V ac, 42V dc

10mV max.

Cat 6a

#### **RJ45 PCB Connector**

#### **Materials**

Voltage rating

Performance

Contact resistance

Coupler Shell Copper Alloy Coupler Plating Nickel Moulding ABS Flammability UL94V-0 Phosphor Bronze 50 micron gold Contact material Contact plating Tin plated Operating Temperature -40°C to +70°C Mating cycles
RoHS 1,000 cycles Compliant **Electrical** 

8 No. Conductors Current rating 1.5A 30V ac, 42V dc Voltage rating  $10m\Omega$  max. Contact resistance Cat 5e Performance

### BUCCANEER FOR DATA

# Standard Buccaneer - Ethernet





Cable Joiner



PX0777

- O IP68 Rating
- O For Sealed In-Line RJ45 Connections
- O Supplied Complete with Coupler
- Shielded (STP) & Unshielded (UTP) versions
- Cat5e Shielded Coupler also available
- Cable Range 3.5 8mm (with glands supplied)





Specifications	PX0777/UTP	PX0777/STP	PX0777/CAT5ESTP	PX0777/CAT6ASTP
Rating: No. of Conductors: Coupler Type: Cable Range:	1.5A, 30V a.c., 42V d.c. 8 Unshielded 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)	1.5A, 30V a.c., 42V d.c. 8 Shielded 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)	1.5A, 30V a.c., 42V d.c. 8 Shielded CAT5e performance 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)	1.5A, 30V a.c., 42V d.c. 8 Shielded CAT6a performance 3.5 - 8mm With glands supplied: 3.5 - 5mm (Blue) 5 - 7mm (Green) 6 - 8mm (Red)
Material:	Glass Filled Polyamide	Glass Filled Polyamide	Glass Filled Polyamide	Glass Filled Polyamide
	UL94V-0	UL94V0	UL94V0	UL94V0
Sealing:	IP68 to BSEN	IP68 to BSEN	IP68 to BSEN	IP68 to BSEN
	60529:1992+A2:2013	60529:1992+A2:2013	60529:1992+A2:2013	60529:1992+A2:2013
	(10m depth for 2 weeks)	(10m depth for 2 weeks)	(10m depth for 2 weeks)	(10m depth for 2 weeks)
Salt Mist	EN60068-2-52 Test Kb Salt Mist	EN60068-2-52 Test Kb Salt Mist	EN60068-2-52 Test Kb Salt Mist	EN60068-2-52 Test Kb Salt Mist
	(Cyclic)	(Cyclic)	(Cyclic)	(Cyclic)
	Marine Severity Level 1	Marine Severity Level 1	Marine Severity Level 1	Marine Severity Level 1
Operating Temp Range:	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Colour:	Black	Black	Black	Black
	Compliant	Compliant	Compliant	Compliant