

Size 150-STA® Pull Tubular Solenoids — 1-1/2" Dia. x 2-1/2"





Performance



| | | | Coil Data | | | | | | |
|---|---------------------------|-----------------------|-------------------------|---|--------------|--------------|--------------|--------------|--|
| • | awg (0XX) ³ | Resistance (@20°C) | # Turns ⁴ | (| VDC (Nom) | VDC (Nom) | VDC (Nom) | VDC (Nom) | |
| ľ | 23 | 5.58 | 1030 | | 9.8 | 13.9 | 19.7 | 31.0 | |
| | 24 | 9.30 | 1344 | | 12.4 | 17.6 | 25.0 | 39.0 | |
| | 25 | 14.90 | 1712 | | 15.7 | 22.0 | 31.0 | 50.0 | |
| | 26 | 24.00 | 2180 | | 19.9 | 28.0 | 40.0 | 63.0 | |
| | 27 | 36.90 | 2680 | | 25.0 | 35.0 | 50.0 | 79.0 | |
| | 28 | 58.40 | 3322 | | 32.0 | 45.0 | 63.0 | 100.0 | |
| | 29 | 87.50 | 4008 | | 39.0 | 56.0 | 79.0 | 124.0 | |
| | 30 | 148.00 | 5292 | | 50.0 | 71.0 | 101.0 | 159.0 | |
| | 31 | 224.00 | 6360 | | 63.0 | 90.0 | 127.0 | 200.0 | |
| | 32 | 344.00 | 7956 | | 78.0 | 110.0 | 155.0 | 246.0 | |
| | 33 | 554.00 | 10070 | 1 | 0.001 | 141.0 | 199.0 | 315.0 | |

- Continuously pulsed at stated watts and duty cycle
- Single pulse at stated watts (with coil at ambient room temperature 20°C)
- Other coil awg sizes available please consult factory
- Reference number of turns

Specifications

| Dielectric Strength | 1000 VRMS | | | | |
|---------------------|---|--|--|--|--|
| Recommended | Maximum watts dissipated by | | | | |
| Minimum Heat Sink | solenoid are based on an unrestricted flow of air at 20°C, with solenoid mounted on the equivalent of an aluminum plate measuring 6" square by 1/8" thick | | | | |
| Coil Resistance | ±5% tolerance | | | | |
| Holding Force | 22.6 lbs (100.4 N) at 20°C | | | | |
| 147 * 1 4 | 17.2 (407.6) | | | | |

Weight 17.2 oz (487.6 g) Plunger Weight 4.04 oz (114.5 g)

How to Order

Add the plunger configuration and the coil awg number to the part number (for example: to order a unit with a 60° plunger without an anti-rotation flat rated for 25 VDC at 25% duty cycle, specify 154660-224.)


Please see www.johnsonelectric.com for our list of stock products available through distribution.

Ledex® Solenoids Fax: 1.937.898.8624 www.johnsonelectric.com 1.937.454.2345

Size 150-STA® Pull Tubular Solenoids — 1-1/2" Dia. x 2-1/2"

Typical Force @ 20°C

All products are RoHS Compliant




Force values for reference only.

Dimensions

Inches (mm)

All solenoids are illustrated in energized state



All specifications subject to change without notice.