Fair-Rite Products Corp.

Your Signal Solution®

## Chip Arrays (2512061027Y0A4)



Part Number: 2512061027Y0A4

## MULTI- LAYER TAPE & REEL

## Part Number System: Example 2512066007Y0A4

25	1206	600	7	Y	0	A4
Chip Suppression	Package Size	Impedance Code	Packaging Code	Material Code	Current Code	Array 4 Lines
Component		600 = 60 Ω	6= Bulk Packed 7= Taped and Reeled 7" Reel 8= Taped and Reeled 13" Reel	Y = Std Signal Speed	0 < 1A	

Fair- Rite offers an effective cost and real estate reduction by our line of chip arrays. Four chip beads, packaged in a 1206 (3216) size, for suppression of conducted EMI where size is at a premium.

Chip arrays have plated contacts, 100% matte tin over a nickel undercoating.

The arrays can accommodate both reflow and wave soldering technologies.

Recommended storage and operating temperature range is -55 °C to 125 °C.

□ □ Chip Bead Kit□ (part number 0199000018) contains the 600 ohm 4 line chip array.

Packaging Options:

□ - Chip arrays are supplied taped and reeled.


Suggested land patterns are in accordance to the IPC-7351.


Weight: 0.03 (g)

Package Size: 1206 (3216)

Dim	mm	mm tol	nominal i	nominal inch inch misc.			
А	0.8	±0.20	0.032	_	_		
В	1.6	$\pm 0.20$	0.063	_	_		
С	3.2	±0.20	0.126	0.126			
D	0.3	±0.20	0.011	0.011			
E	0.8	±0.10	0.032	_	_		
F	0.04	±0.15	0.018		_		
Land P	atterns	5					
V	ľ	W	Х	Y	Ζ		
0.70		1.30	0.50	0.60	0.80		
(0.028")		0.051")	(0.020")	(0.024")	(0.032")		

Reel Informat	tion			
Tape Width mm	Pitch mm	Parts 7" Reel	Parts 13" Reel	Parts 14" Reel
8	4	3000	-	-







									Land Patterns				Reel Info		
Pkg. Size	А	В	C	D	E	F	Wt. (g)	۷	W (ref)	X	Y	Z	Tape Width mm	Pite mr	
206 216)	0.8±0.2 0.032	1.6±0.2 0.063	3.2±0.2 0.126		0.8±0.1 0.032	0.45±0.2 0.018	0.03	0.7 0.028	1.3 0.051	0.5 0.020	0.6 0.024	0.8 0.032	8	4	

## **Chart Legend**


+ Test frequency

Typical Im	pedan	ce (	Ω)				
50 MHz	770						
$100 \mathrm{MHz}^{+}$	1000	±25	%				
500 MHz	400						
1000 MHz	200						
Electrical Properties							
Max DCR (Ω)	0.7						
Max Currer (mA)	nt	50					


Chip arrays are controlled for impedance. The impedance values listed are typical values. The nominal impedance with a +/-25% tolerance is specified for the + marked 100 MHz frequency. Chip arrays are measured for impedance on the HP 4291A and fixture HP 16192A.

The maximum voltage between adjacent beads is 5V.

Chip arrays are 100% tested for impedance and dc resistance.



Impedance, reactance, and resistance vs. frequency.



Impedance vs. frequency with dc bias.

	Fai	r- Rite Products C	orp.		One Commerci	al Rov	v, Wallkill, New York 125	89-02	288
888-324-7748		845-895-2055		Fax	:: 845-895-2629		ferrites@fair- rite.com		www.fair- rite.com