

Sound level measuring instrument

Model testo 815



Application:

Ideally suited for control measurements in air-conditioning or heating applications, on combustion plants as well as for assessing noise pollution on machines and at the workplace.

Version:

- Maximum and minimum value memory
- Switchable time evaluation, fast/slow

Advantage:

- Frequency evaluation according to characteristic curve A and C
- Easy to adjust



Art. no.	46210 100
Min./max. sound-pressure-level measuring range	32-130 dB
Digit increment, sound-pressure level	1 dB
Sound-pressure-level error limit (+/-)	1 dB
Min./max. working temperature	0 to 40 °C

EAN-Code

4029547001864