

## Front-mounted sliding door, 3-part

For HK tool shelf

### Application:

The sliding doors can be used to turn two shelf bays into one cabinet with sliding doors.

### Execution:

- From sheet steel, canted
- Projection depth 95 mm
- Drawers or fixed or pull-out, height-adjustable shelves can be installed behind the front-mounted sliding doors
- When requesting/ordering, please indicate the RAL colours required.

<b>Art. no.</b>	<b>50548 610</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	505486 10
<b>Colour</b>	Optional
<b>Suitable for width</b>	1400 mm
<b>Surface</b>	Powder-coated
<b>Material</b>	Sheet steel
<b>Gross Weight</b>	0.010 kg
<b>Product Group</b>	501



### EAN

4039247697458