

### **ADELIA-50-M**

~24° medium beam

### **SPECIFICATION:**

Dimensions Ø 49.8 mm
Height 18 mm
Fastening snaps
ROHS compliant yes 1



### **MATERIALS:**

ComponentTypeMaterialComponentADELIA-50-MReflectorAluminiummedical

ColourFinishCoatingmetalglossAnodized

### **ORDERING INFORMATION:**

Component


C18316\_ADELIA-50-M

» Box size: 350 x 280 x 310 mm

**Qty in box MOQ MPQ Box weight (kg)** 2000 100 12.2



# **PRODUCT** C18316\_ADELIA-50-M




See also our general installation guide: www.ledil.com/installation\_guide



### bridgelux

LED V10 Gen 8
FWHM / FWTM 22.0° / 64.0°
Efficiency 92 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C18432\_ADELIA-ADAPTER-C Bender Wirth: 634b Hekla




### bridgelux.

LED V10 Gen 8
FWHM / FWTM 24.0° / 77.0°
Efficiency 91 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C18431\_ADELIA-ADAPTER-B

BJB: 47.360.1020



#### bridgelux

LED V18 Gen 8
FWHM / FWTM 38.0° / 94.0°
Efficiency 83 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C18432 ADELIA-ADAPTER-C

C18432\_ADELIA-ADAPTER-C Bender Wirth: 639b Hekla XL

### bridgelux.

LED V22 Gen 8
FWHM / FWTM 40.0° / 95.0°
Efficiency 79 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C18432\_ADELIA-ADAPTER-C Bender Wirth: 631b Hekla XL




bridgelux

LED V6 HD Gen 7 FWHM / FWTM 19.1° / 42.2 + 43.2°

Efficiency 95 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17435\_HEKLA-G2-C C18432\_ADELIA-ADAPTER-C




**CITIZEN** 

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 24.0° / 80.0°
Efficiency 92 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17435\_HEKLA-G2-C C18432\_ADELIA-ADAPTER-C



CREE - LED

 LED
 CMU10xx


 FWHM / FWTM
 24.0° / 81.0°

 Efficiency
 91 %

 Peak intensity
 2.6 cd/lm

LEDs/each optic 1
Light colour White
Required components:

C18431\_ADELIA-ADAPTER-B




CREE & LED

LED CXA/B 15xx
FWHM / FWTM 22.0° / 71.0°
Efficiency 90 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17436\_HEKLA-G2-D

C18432\_ADELIA-ADAPTER-C






### CREE \$\text{LED}

LED CXA/B 1830  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 30.0° / 88.0° Efficiency 88 % Peak intensity 1.7 cd/lm LEDs/each optic Light colour White

Required components:

C18432\_ADELIA-ADAPTER-C Bender Wirth: 637b Hekla




# **SAMSUNG**

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 24.1° / 81.5 + 80.4°

Efficiency 92 % Peak intensity 2.5 cd/lm LEDs/each optic 1 White Light colour Required components: F17435\_HEKLA-G2-C

C18432\_ADELIA-ADAPTER-C




## **SAMSUNG**

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 24.0° / 80.0° Efficiency 91 % Peak intensity 2.6 cd/lm LEDs/each optic 1 Light colour White

Required components: F17435\_HEKLA-G2-C

C18432\_ADELIA-ADAPTER-C




# **SAMSUNG**

LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 33.0° / 90.0° Efficiency 88 % Peak intensity 1.6 cd/lm LEDs/each optic White Light colour Required components:

F17438 HEKLA-G2-I

C18432\_ADELIA-ADAPTER-C






# **SAMSUNG**

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 34.2° / 90.5°
Efficiency 90 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:

F17438\_HEKLA-G2-I

C18432\_ADELIA-ADAPTER-C





# PRODUCT DATASHEET C18316\_ADELIA-50-M

### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

### LEDiL Oy

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

# Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

www.ledil.com/ where\_to\_buy