

Product type designation

Product description

PROFIBUS PCF Fiber Optic standard cable

PCF fiber-optic cable with plastic cladding, preferred length, preassembled

SIMATIC NET, PROFIBUS PCF FIBER OPTIC, WITH 4 PCF BFOC CONNECTORS L = 100 M



Suitability for use	Cable for indoor applications
Version of the assembled FO cable	Assembled with four BFOC connectors
Cable designation	I-V(ZN)Y 2K 200/230
Cable length	100 m

Optical data

Damping ratio per length	
<ul style="list-style-type: none"> • at 650 nm / maximum • at 660 nm / maximum 	10 dB/km
Bandwidth length product	
<ul style="list-style-type: none"> • at 650 nm 	17 GHz·m

Mechanical data

Number of fibers / per FOC core	1
Number of FO cores / per FOC cable	2
Version of the FO conductor fiber	Step index fiber 200/230 µm
Outer diameter	
<ul style="list-style-type: none"> • of the optical fibers • of the optical fiber sheath • of the FOC core sheath 	200 µm 230 µm 2.2 mm
Symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
Outer diameter / of the cable	4.7 mm
Material	

<ul style="list-style-type: none"> • of the fiber-optic cable core • of the optical fiber sheath • of the FOC core sheath • of the fiber-optic cable sheath • of the strain relief 	Quartz glass fluoridated special polymer PVC PVC Kevlar fibers
Color	
<ul style="list-style-type: none"> • of the FOC core sheath • of cable sheath 	Orange/black Violet
Bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	47 mm 70 mm
Tensile load / during operation / maximum	200 N
Short-term shear force per length	100 N/cm
Weight per length	22 kg/km

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	-30 ... +70 °C -30 ... +70 °C -30 ... +70 °C -5 ... +50 °C
Burning behavior	Flame-resistant acc. to IEC 60332-1-2
Chemical resistance	
<ul style="list-style-type: none"> • to mineral oil • to grease 	Conditional resistance Conditional resistance
Radiological resistance / to UV radiation	Not resistant
Protection class IP	IP20

Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> • halogen-free • silicon-free 	No Yes
Product component / Rodent protection	No
Cable length	
<ul style="list-style-type: none"> • for PCF FOC / with PROFIBUS / maximum 	400 m

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> • RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication 	http://www.siemens.com/snst http://www.siemens.com/simatic-net

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

16.03.2015