

## Datenblatt - Fiche technique - Data sheet **11.09.4338**




ROLINE Cinch-Verbindungskabel duplex ST/ST, 10m

ROLINE Câble 2x RCA M/M, 10m

ROLINE Cinch Extension Cable, 2x RCA M-M, 10 m

# 1. DIMENSION




Item no.	L
11.09.4333	2500±50
11.09.4336	5000±150
11.09.4338	10000±200


# 2. PART LISTS

4	CABLEø2.7*2.7	PVC (BLACK)
3	RCA PLUG CAP	PVC (RED)(WHITE)
2	RCA RING	C2680R NICKEL PLATED
1	RCA PIN	C2680R NICKEL PLATED
NO.	PART'S NAME	MATERIAL. FINISHED. COLOR

A A	表 FINIS 顏	HED 色	Rotronic Co., Ltd.
<u>^</u> \$\alpha\	COL 厚 THICK	度	
A	戾 PROC	理 ESS	11.09.4333.36.38
記號 MARK 修正 REVISION	日期 擔當承認 MATE DATE SIGN APPO 公	RIAL	지 않는 1년
APPROVED BY 檢 CHECKEO BY 設 DESIGN	DRAWN BY TOLER	例	
103·4·30.	29 SCA	位 mm	SP-1314 1/5

## 3. RCA PLUG DIMENSION






\$	STS-3
L <u>≤</u> 4	± 0.2
4 <l<_16< td=""><td>± 0.3</td></l<_16<>	± 0.3
16 <l<<u>_63</l<<u>	± 0.4
63 <l<<u>250</l<<u>	± 0.5
250 <l< td=""><td>± 0.7</td></l<>	± 0.7

名	DESCRIPTION.	<b>B</b>	DRAWN NO.	SHEET
稱	AUDIO CONNECTION CABLE	號	SP-1314	2

# 4 CORD SPEC



DESCRIPTION		MATERIAL	SPECIFICATION	
1	CONDUCTOR	OFC COPPER	0.12*10*2C	
2	CORE DIA.	PE(R)(W)	$\varphi 1.3^{\pm 0.1}*2C$	
3	SHIELD WIRE	OFC COPPER	0.12*28*2C	
	JACKET	PVC	$\varphi 2.7^{\pm 0.1} *2.7^{\pm 0.1} mm$	
	NON MIGRATION	BLACK	FOR ABS PLATE	

名	DESCRIPTION.				圖	DRAWN NO.	SHEET
稱		AUDIO	CONNECTING	CABLE	號	SP-1314	3

## 5. CHARACTERISTICS

#### STANDARD ATMOSPHERIC CONDITIONS

UNLESS OTHERWISE SPECIFIED, THE STANDARD RANGE OF ATMOSPHERIC CONDITIONS FOR MAKING MEASUREMENTS AND TESTS ARE AS FOLLOWS:

AMBIENT TEMPERATURE : 5°C TO 35°C RELATIVE HUMIDITY : 45% TO 85% AIR PRESSURE : 86KPa TO 106KPa

IF THERE IS ANY DOUBT ABOUT THE RESULTS. MEASUREMENTS SHELL BE MADE WITHIN THE FOLLOWING LIMITS:

AMBIENT TEMPERATURE : 20±2°C


RELATIVE HUMIDITY : 60% TO 70%

AIR PRESSURE : 86KPa TO 106KPa

NO	ITEMS	CONDITIONS	SPECIFICATIONS
1	APPEARANCE		NO DEFECTS SUCH AS CRACKS, SCRATCHES OR BLEMISHES.
2	INSERTION FORCE WITHDRAWAL FORCE	MEASUREMENT SHALL BE MADE AFTER INSERTING INTO ITS MATING PLUG OR SOCKET 3 TIMES. RCA PLUG	2.94N(0.3Kgf) ~ 29.4N(3.0Kgf)
3	TENSLLE STRENGTH	BETWEEN CABLE & CONNECTOR 29.4N(3.0KGF), 1 MINUTE	NO DAMAGE SUCH AS DISPLACEMENT OR INSULATION DAMAGE,ETC
4	FLEXING TEST	500G, 60°, 1000TURNS 15~20/PER MIN TURNS	NO DAMAGE SUCH AS DISPLACEMENT OR INSULATION DAMAGE,ETC
5	INSULATION RESISTANCE	DC 250V 1 MINUTE BETWEEN CONDUCTORS	50 MΩ OR MORE
6	DLELECTRIC STRENGTH	AC 250V SHALL BE APPLLED FOF 1 MINUTE WITH TRIP CURRENT 2 mA BETWEEN CONDUCTORS	WITHOUT DAMAGE SACH AS ELECTRIC BREAKDOWN
7	ABS NON-MIGRATION	TEMPERATURE : 54 ± 1 °C TIME : 24± 1H WEIGHT : 500 ±25 G	WHEN VISUALLY INSPECTED. ANY STAINING OF THE AREA OF THE ABS THAT WAS IN CONTACT WITH THE TEST PIECES SHALL HARDLY BE RECOGNIZED

名	DESCRIPTION.			圖 DRAWN NO.		SHEET
稱	AUDIO	CONNECTION	CABLE	號	SP-1314	4

## 6. PACKAGE



Item no.	(L)
11.09.4333	156
11.09.4336	156
11.09.4338	156

DESCRIPTION. AUDIO CONNECTION CABLE  $\frac{8}{5}$  DRAWN NO. SP-1314 SHEET 5