


## DG S 440 (952 075)


- Multi-purpose surge arrester consisting of a base element and a plug-in protection module
- High discharge capacity due to heavy-duty zinc oxide varistor
- High reliability due to "Thermo Dynamic Control" SPD monitoring device



Figure without obligation



Basic circuit diagram DG S 440



Dimension drawing DG S 440

Pluggable single-pole surge arrester consisting of a base part and a plug-in protection module.

| Type<br>Part No.   | DG S 440<br>952 075                                       |
|--|---|
| SPD according to EN 61643-11 / IEC 61643-11  | type 2 / class II   |
| Energy coordination with terminal equipment ( $\leq 10$ m)                                   | type 2 + type 3   |
| Nominal voltage (a.c.) ( $U_N$ )   | 400 V (50 / 60 Hz)  |
| Max. continuous operating voltage (a.c.) ( $U_c$ )   | 440V (50 / 60 Hz)   |
| Max. continuous operating voltage (d.c.) ( $U_c$ )   | 585 V   |
| Nominal discharge current (8/20 $\mu$ s) ( $I_n$ )   | 20 kA   |
| Max. discharge current (8/20 $\mu$ s) ( $I_{max}$ )  | 40 kA   |
| Voltage protection level ( $U_P$ )   | $\leq 2$ kV   |
| Voltage protection level at 5 kA ( $U_P$ )   | $\leq 1.7$ kV   |
| Response time ( $t_a$ )  | $\leq 25$ ns  |
| Max. mains-side overcurrent protection   | 125 A gG  |
| Short-circuit withstand capability for max. mains-side overcurrent protection ( $I_{SCCR}$ ) | 25 kA <sub>rms</sub>                                      |
| Temporary overvoltage (TOV) ( $U_T$ ) – Characteristic                                       | 580 V / 5 sec. – withstand                                |
| Temporary overvoltage (TOV) ( $U_T$ ) – Characteristic                                       | 765 V / 120 min. – safe failure                           |
| Operating temperature range ( $T_U$ )  | -40 °C ... +80 °C   |
| Operating state / fault indication   | green / red   |
| Number of ports  | 1   |
| Cross-sectional area (min.)  | 1.5 mm <sup>2</sup> solid / flexible                      |
| Cross-sectional area (max.)  | 35 mm <sup>2</sup> stranded / 25 mm <sup>2</sup> flexible |
| For mounting on  | 35 mm DIN rails acc. to EN 60715                          |
| Enclosure material   | thermoplastic, red, UL 94 V-0                             |
| Place of installation  | indoor installation                                       |
| Degree of protection   | IP 20   |
| Capacity   | 1 module(s), DIN 43880                                    |
| Approvals  | KEMA, VDE, UL, CSA  |
| Weight   | 142 g   |
| Customs tariff number  | 85363030  |
| GTIN   | 4013364109896   |
| PU   | 1 Stk   |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.