

## ESD shelf trolley with 5 load areas

Height 1800 mm, load capacity 600 kg

### Application:

For transporting non-stacking goods and materials, for continuous use in industrial applications. Electrically conductive design.

### Version:

- Welded steel tube and profile steel, bolted construction
- Shelves made of electrically conductive wooden plate in accordance with DIN 68765, light grey.
- 1 fixed shelf

### Advantage:

- Reliable dissipation of electric charges thanks to continuously conductive structure
- Robust design and high load capacity ensure a long service life even when used for high industrial loads
- Multiple load areas provide ample storage space for non-stacking goods and crates
- FETRA plug-and-screw design allows trolleys and accessories to be modified easily
- Large high-quality castors for good running properties



<b>Art. no.</b>	<b>50268 729</b>
<b>Load-carrying capacity</b>	600 kg
<b>Load-carrying capacity of loading surfaces</b>	50 kg
<b>Colour</b>	Slate grey RAL 7015
<b>Material of loading surface</b>	Wood, electroconductive
<b>Number of loading surfaces</b>	4
<b>Loading surface size</b>	1000 x 700 mm
<b>Loading surface length</b>	1000 mm
<b>Loading-surface width</b>	700 mm
<b>Length</b>	1169 mm
<b>Width</b>	709 mm
<b>Height</b>	1800 mm
<b>Length x width x height</b>	1169 x 709 x 1800 mm
<b>Surface</b>	Powder-coated
<b>Loading-surface height</b>	276 mm
<b>Loading-surface height 2</b>	576 mm
<b>Loading-surface height 3</b>	876 mm
<b>Loading-surface height 4</b>	1176 mm
<b>Loading-surface height 5</b>	1476 mm
<b>Made in</b>	Germany
<b>EN standard</b>	1757-3
<b>With wheel lock</b>	Yes
<b>Wheel diameter</b>	200 mm
<b>Material of wheel</b>	TPE-ESD
<b>Wheel width</b>	40 mm
<b>Total stop optional</b>	Yes
<b>Number of fixed rollers</b>	2
<b>Number of steering rollers</b>	2

### EAN-Code

4017976093420