

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: UHU por**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Adhesives
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
UHU GmbH & Co.KG
Herrmannstraße 7
D-77815 Bühl (Baden)
Tel.:0049-(0)7223-284-0
email: sds@uhu.boltongroup.com
- Fax: 0049-(0)7223-284-245
- **Further information obtainable from:** UHU QESH
- **1.4 Emergency telephone number:**
Tel.: + 49 (0) 30/19240 (Notruf)
Tel.: + 49 (0) 72 23/28 40

- England and Wales (NHS Direct) 111
Schottland (NHS 24) 111

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.



GHS09 environment

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.
STOT SE 3 H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 1)

Hazard pictograms


GHS02 GHS07 GHS09

Signal word Danger

Hazard-determining components of labelling:

heptane

Hazard statements

H225 Highly flammable liquid and vapour.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P210 Keep away from open flames. - No smoking.

P261 Avoid breathing vapours.

P302+P352 IF ON SKIN: Wash with plenty of water.

P501 Dispose of contents/container in accordance with national regulations.

2.3 Other hazards
Results of PBT and vPvB assessment
PBT: Not applicable.

vPvB: Not applicable.





SECTION 3: Composition/information on ingredients

3.2 Mixtures
Description:

Mixture of substances listed below with nonhazardous additions.

Adhesive

Dangerous components:

EC number: 927-510-4	heptane	50-100%
Reg.nr.: 01-2119475515-33-005	 Flam. Liq. 2, H225;  Asp. Tox. 1, H304;  Aquatic Chronic 2, H411;  Skin Irrit. 2, H315; STOT SE 3, H336	

Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures
General information: No special measures required.

(Contd. on page 3)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 2)

- **After inhalation:**
In case of unconsciousness place patient stably in side position for transportation.
Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture**
In case of fire, the following can be released:
Carbon monoxide (CO)
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Send for recovery or disposal in suitable receptacles.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.

(Contd. on page 4)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 3)

Protect against electrostatic charges.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** Store in a cool location.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:**

Keep container tightly sealed.

Store in cool, dry conditions in well sealed receptacles.

· **Storage class:** 3

· **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **DNELs**

heptane

Oral	Consumer DNEL, longterm oral	149 mg/kg bw/day
Dermal	Consumer DNEL, longterm dermal	149 mg/kg bw/day
Inhalative	Consumer DNEL, longterm inhalation	477 mg/m ³

· **PNECs**

heptane

PNEC Fresh water	mg/l
PNEC Marine water	mg/l
PNEC Soil	mg/kg

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

· **Respiratory protection:**

Not necessary if room is well-ventilated.

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

(Contd. on page 5)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 4)

· **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves

· **Material of gloves**

glove material: butyl rubber

thickness of the glove material: 0,6 - 0,8 mm

breakthrough time (maximum wearing time): 60 - 120 min.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**

Goggles recommended during refilling



Tightly sealed goggles

Goggles recommended during refilling

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Fluid

Colour: Yellowish

· **Odour:** Characteristic

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/freezing point: Undetermined.

Initial boiling point and boiling range: 83-105 °C

· **Flash point:** -4 °C

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 5)

· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	0 °C
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	0.0 Vol %
Upper:	0.0 Vol %
· Vapour pressure:	Not determined.
· Density at 20 °C:	0.80529 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic at 20 °C:	8000 mPas
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	69.2 %
VOC (EC)	69.19 %
Solids content:	30.8 %
· 9.2 Other information	All relevant physical data were determined for the mixture. All non determined data are not measurably or not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.

(Contd. on page 7)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 6)

- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes skin irritation.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Danger to drinking water if even small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

EU-EN

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 7)

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Disposal must be made according to official regulations.

· **European waste catalogue**

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
-----------	--

· **Uncleaned packaging:**

· **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, IMDG, IATA**

UN1133

· **14.2 UN proper shipping name**

· **ADR**

1133 ADHESIVES, ENVIRONMENTALLY HAZARDOUS

1133 KLEBSTOFFE, UMWELTGEFÄHRDEND, Sondervorschrift 640H

· **IMDG**

ADHESIVES (heptane), MARINE POLLUTANT

· **IATA**

ADHESIVES

· **14.3 Transport hazard class(es)**

· **ADR, IMDG**



· **Class**

3 Flammable liquids.

· **Label**

3

· **IATA**



· **Class**

3 Flammable liquids.

· **Label**

3

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 8)

· 14.4 Packing group	III
· ADR, IMDG, IATA	
· 14.5 Environmental hazards:	Product contains environmentally hazardous substances: heptane
· Marine pollutant:	Yes
	Symbol (fish and tree)
· Special marking (ADR):	Symbol (fish and tree)
· 14.6 Special precautions for user	Warning: Flammable liquids.
· Danger code (Kemler):	-
· EMS Number:	F-E,S-D
· Stowage Category	A
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR	
· Limited quantities (LQ)	5L
· Excepted quantities (EQ)	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· Transport category	3
· Tunnel restriction code	E
· IMDG	
· Limited quantities (LQ)	5L
· Excepted quantities (EQ)	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· UN "Model Regulation":	UN 1133 ADHESIVES, 3, III, ENVIRONMENTALLY HAZARDOUS

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category**
E2 Hazardous to the Aquatic Environment
P5c FLAMMABLE LIQUIDS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 200 t

(Contd. on page 10)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 26.06.2019

Version number 33

Revision: 26.06.2019

Trade name: UHU por

(Contd. of page 9)

- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

- H225 Highly flammable liquid and vapour.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.

· **Department issuing SDS:** UHU QESH

· **Contact:** Dr. C. Hanf

· **Abbreviations and acronyms:**

- ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- VOC: Volatile Organic Compounds (USA, EU)
- DNEL: Derived No-Effect Level (REACH)
- PNEC: Predicted No-Effect Concentration (REACH)
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Flam. Liq. 2: Flammable liquids – Category 2
- Skin Irrit. 2: Skin corrosion/irritation – Category 2
- STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- Asp. Tox. 1: Aspiration hazard – Category 1
- Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

- *** Data compared to the previous version altered.**