

Connector, XLR Receptacle, 3 Pos

multicomp PRO

**RoHS
Compliant**

Specifications:

Electrical:

Contact rating : 15A at 125V AC
 Contact resistance : 5mΩ Max.
 Insulation resistance : 5,000MΩ Min. at 500V DC
 Dielectric strength : 1,400V AC
 Capacitance : 4pF Max.

Mechanical:


Insertion force : 1 to 8kg
 Withdrawal force : 1 to 8kg

Environmental:

Operating temperature : -55°C to 70°C



Diagram



Item	Part	Material	Finish
1	Housing	Zinc Die Cast	Nickel
2	Insert Insulator	PP0-1	Grey
3	Socket	Phosphor Bronze	Silver
4	Cable Relief	PVP	Matte

Part Number Table

Description	Part Number
3 Contact female XLR Audio Cord Plug	SPC21424

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO