

MIRELLA-G2-WW

~50° wide beam compatible with LEDiL HEKLA

TECHNICAL SPECIFICATIONS:

Dimensions Ø 49.9 mm Height 22.6 mm Fastening socket Colour metal

Box size 480 x 280 x 300 mm

Box weight 3.7 kg 336 pcs Quantity in Box yes 🕕 ROHS compliant




MATERIAL SPECIFICATIONS:


Component **Type** Material Colour Coating


MIRELLA-G2-WW Reflector PC metal






2/21







PHOTOMETRIC DATA (MEASURED):


CITIZEN


LED CLC020 Series (Dim-To-Warm)

FWHM 49.0° 77 % Efficiency Peak intensity 1.100 cd/lm LEDs/each optic 1

Light colour White Required components:

C16142_HEKLA-SOCKET-K





CITIZEN


LED CLC020 Series (Dim-To-Warm)

FWHM 50.0° 70 % Efficiency Peak intensity 0.840 cd/lm

LEDs/each optic 1 Light colour White Required components:

C16142_HEKLA-SOCKET-K C13723_MIRELLA-RZL Bender Wirth: 487 Typ L8






LED CLL02x/CLU02x (LES10)

FWHM 59.0° Efficiency 82 % Peak intensity 0.970 cd/lm

LEDs/each optic 1 Light colour White Required components: F15255_HEKLA-SOCKET-C






CITIZEN

CLU700/701 **FWHM** 45.0° Efficiency 85 % 1.300 cd/lm Peak intensity

LEDs/each optic 1 White Light colour Required components:

F15255_HEKLA-SOCKET-C





PHOTOMETRIC DATA (MEASURED):

CITIZEN

 LED
 CLU700/701

 FWHM
 44.0°


 Efficiency
 85 %

 Peak intensity
 1.300 cd/lm

Peak intensity 1.300 cd/ LEDs/each optic 1 Light colour White Required components:

F15255_HEKLA-SOCKET-C C13723_MIRELLA-RZL







CITIZEN

LED CLU710/711
FWHM 53.0°
Efficiency 80 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1

Light colour White
Required components:
F15859_HEKLA-SOCKET-I






CITIZEN

LED CLU7A2 (LES 4.2mm)

FWHM 38.0°
Efficiency 83 %
Peak intensity 1.400 cd/lm

LEDs/each optic 1 Light colour White Required components: F15255_HEKLA-SOCKET-C







CITIZEN

LED LCN-C01B (Tunable White)

FWHM 50.0°
Efficiency 70 %
Peak intensity 0.810 cd/lm
LEDs/each optic 1

Light colour White
Required components:
C16142_HEKLA-SOCKET-K
C13723_MIRELLA-RZL
Bender Wirth: 481 Typ L8






PHOTOMETRIC DATA (MEASURED):

CREE 💠

LED CXA/B 15xx
FWHM 51.0°
Efficiency 89 %
Peak intensity 1.200 cd/lm
LEDs/each optic 1
Light colour White

Required components:
F15256_HEKLA-SOCKET-D





MUMILEDS


LED LUXEON CoB 1202/1203

FWHM 56.0°
Efficiency 83 %
Peak intensity 1.000 cd/lm

LEDs/each optic 1
Light colour White
Required components:

F15858_HEKLA-SOCKET-H






MILEDS

LED LUXEON CoB 1202/1203

FWHM 56.0°
Efficiency 83 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1

Light colour White
Required components:
F15858_HEKLA-SOCKET-H
C12479_MIRELLA-DL






DESCRIPTION


LED LUXEON CoB 1202HD

FWHM 48.0° Efficiency 83 % Peak intensity 1.160 cd/lm

LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G



PHOTOMETRIC DATA (MEASURED):






C13723_MIRELLA-RZL Bender Wirth: 490 Typ L8


LED CDM-6 (Dim-To-Warm)


FWHM 43.0°
Efficiency 77 %
Peak intensity 1.200 cd/lm
LEDs/each optic 1

Light colour White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 490 Typ L8









PHOTOMETRIC DATA (MEASURED):

WNICHIA


LED NVCWJ024Z-V1MT: COB J-Type Tunable White

FWHM 51.0° 69 % Efficiency Peak intensity 0.800 cd/lm LEDs/each optic 1

Required components: C16142_HEKLA-SOCKET-K C13723_MIRELLA-RZL Bender Wirth: 498 Typ L8

White





WNICHIA


Light colour

LED NVCWJ024Z-V1MT: COB J-Type Tunable White

FWHM 52.0° 77 % Efficiency 1.000 cd/lm Peak intensity LEDs/each optic 1

Light colour White Required components: C16142_HEKLA-SOCKET-K Bender Wirth: 498 Typ L8






OSRAM Opto Semiconductors

LED Soleriq S9 **FWHM** 39.0° Efficiency 91 % Peak intensity 1.500 cd/lm

LEDs/each optic 1 Light colour White Required components:

F15255_HEKLA-SOCKET-C






LED Fortimo SLM L09 CoB

FWHM 55.0° 74 % Efficiency 0.800 cd/lm Peak intensity

LEDs/each optic 1 White Light colour Required components:

F15858_HEKLA-SOCKET-H C13723_MIRELLA-RZL







PHOTOMETRIC DATA (MEASURED):

PHILIPS

Light colour


LED Fortimo SLM L09 CoB

White

FWHM 57.0°
Efficiency 82 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1

Required components: F15858_HEKLA-SOCKET-H





PHILIPS

LED Fortimo SLM L13 CoB

FWHM 54.0° Efficiency 71 % Peak intensity 0.740 cd/lm

LEDs/each optic 1
Light colour White
Required components:

C16142_HEKLA-SOCKET-K C13723_MIRELLA-RZL Bender Wirth: 432 Typ L8



PHILIPS


LEDs/each optic 1


LED Fortimo SLM L13 CoB

FWHM 54.0° Efficiency 71 % Peak intensity 0.740 cd/lm

Light colour White
Required components:
C16142_HEKLA-SOCKET-K
C13723_MIRELLA-RZL

Bender Wirth: 432 Typ L8





PHILIPS


LED Fortimo SLM L13 CoB

FWHM 58.0° Efficiency 77 % Peak intensity 0.800 cd/lm

LEDs/each optic 1 Light colour White Required components: C16142_HEKLA-SOCKE

C16142_HEKLA-SOCKET-K Bender Wirth: 432 Typ L8






PHOTOMETRIC DATA (MEASURED):

LED Fortimo SLM L13 CoB

FWHM 58.0° 77 % Efficiency Peak intensity 0.840 cd/lm LEDs/each optic 1

Light colour White Required components: C16142_HEKLA-SOCKET-K Bender Wirth: 432 Typ L8






SAMSUNG

LED COB D Series LES 14.5 mm

FWHM 62.0° 79 % Efficiency Peak intensity 0.800 cd/lm LEDs/each optic 1

Light colour White Required components: F15859_HEKLA-SOCKET-I






SAMSUNG

COB D Series LES 14.5 mm LED

FWHM 57.0° Efficiency 71 % Peak intensity 0.710 cd/lm

LEDs/each optic 1 Light colour White Required components: F15859_HEKLA-SOCKET-I C13723_MIRELLA-RZL





SAMSUNG


LED COB D Series LES 14.5 mm

White

FWHM 62.0° Efficiency 75 % 0.760 cd/lm Peak intensity LEDs/each optic 1

Light colour Required components: F15859_HEKLA-SOCKET-I C13333_MIRELLA-CL





PHOTOMETRIC DATA (MEASURED):


SAMSUNG

LED COB D Series LES 14.5 mm

FWHM 60.0° Efficiency 73 % Peak intensity 0.740 cd/lm LEDs/each optic 1

Light colour White Required components: F15859_HEKLA-SOCKET-I C12479_MIRELLA-DL






LED LC010C G2 **FWHM** 45.0° 82 % Efficiency 1.200 cd/lm Peak intensity

LEDs/each optic 1 Light colour White Required components: F15255_HEKLA-SOCKET-C





SAMSUNG

LED LC010T (Tunable White)

FWHM 52.0° Efficiency 78 % Peak intensity 1.052 cd/lm


LEDs/each optic 1

Light colour **Tunable White**

Required components:

C16142_HEKLA-SOCKET-K C14658_BARBARA-RZ-LENS Bender Wirth: 501 Typ L8





SAMSUNG

LED LC010T (Tunable White)


FWHM 48.0° 82 % Efficiency 1.165 cd/lm Peak intensity LEDs/each optic 1

Tunable White Light colour

Required components:

C16142_HEKLA-SOCKET-K Bender Wirth: 501 Typ L8





PHOTOMETRIC DATA (MEASURED):


SAMSUNG

LED LC020C FWHM 56.0° Efficiency 83 % Peak intensity 1.000 cd/lm

LEDs/each optic 1 Light colour White Required components:

F15848_HEKLA-SOCKET-G






SAMSUNG

LED LC020C G2
FWHM 55.0°
Efficiency 81 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1

Light colour White
Required components:
F15859_HEKLA-SOCKET-I






TRIDONIC

LED SLE G7 LES09

FWHM 54.0° Efficiency 76 % Peak intensity 0.860 cd/lm

LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C
C13723_MIRELLA-RZL






TRIDONIC

LED SLE G7 LES09

FWHM 56.0°
Efficiency 84 %
Peak intensity 1.100 cd/lm

LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



PHOTOMETRIC DATA (MEASURED):

Required components:


F15255_HEKLA-SOCKET-C

TRIDONIC LED SLE G7 LES13 **FWHM** 61.0° Efficiency 79 % Peak intensity 0.850 cd/lm LEDs/each optic 1 Light colour White Required components: F15859_HEKLA-SOCKET-I **TRIDONIC** LED SLE G7 LES13 **FWHM** 56.0° 71 % Efficiency Peak intensity 0.740 cd/lm LEDs/each optic 1 Light colour White Required components: F15859_HEKLA-SOCKET-I C13723_MIRELLA-RZL **XICATO** LED XOB 6 mm **FWHM** 53.0° Efficiency 80 % Peak intensity 0.937 cd/lm LEDs/each optic 1 Light colour White Required components: F15255_HEKLA-SOCKET-C C13723_MIRELLA-RZL **XICATO** XOB 6 mm **FWHM** 44.0° Efficiency 88 % 1.325 cd/lm Peak intensity LEDs/each optic 1 White Light colour



PHOTOMETRIC DATA (MEASURED):

XICATO LED XOB 9.8 mm **FWHM** 55.0° Efficiency 81 % Peak intensity 0.890 cd/lm LEDs/each optic 1 Light colour White Required components: F15255_HEKLA-SOCKET-C C13723_MIRELLA-RZL




XICATO

LED **XOB 9.8 mm FWHM** 55.0° Efficiency 88 % Peak intensity 1.114 cd/lm LEDs/each optic 1

White Light colour Required components:







PHOTOMETRIC DATA (SIMULATED):

bridgelux.

 LED
 VERO13


 FWHM
 53.0°

 Efficiency
 83 %

 Peak intensity
 1.100 cd/lm

LEDs/each optic 1 Light colour White Required components:

C16142_HEKLA-SOCKET-K




WNICHIA

LED COB L-Type (LES 11)

FWHM 61.0° Efficiency 88 % Peak intensity 0.990 cd/lm

LEDs/each optic 1 Light colour White Required components:

F15858_HEKLA-SOCKET-H





GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy