

## Platform scales DE-D



### Application:

For versatile use in various locations such as production, warehousing and shipping.

### Execution:

- Dual range scales with automatic switch-over
- Display unit (degree of protection IP65) with 1.5 m cable
- Options: Stand for display unit
- Freely-programmable weighing unit, e.g. displays in thread length g/m, paper weight g/m<sup>2</sup>
- Formulation function for weighing different components
- Backlit LCD display with 25 mm digit size

### Advantage:

- Dual measurement display for finer digit increment and higher accuracy in the initial weighing range
- **Versatile positioning of display unit, free-standing or bolted to scales**

### Delivery:

Mains adapter



<b>Art. no.</b>	<b>44618 280</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	DE 150K20DL
<b>Type description</b>	DE 150K20DL
<b>Max. weight measuring range</b>	60 kg
<b>Max. weight measuring range 2</b>	150 kg
<b>Digit increment, weight</b>	20 g
<b>Digit increment 2, weight</b>	50 g
<b>Plate size</b>	522 x 403 mm
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	40 g
<b>Reproducibility</b>	20 g
<b>Reproducibility 2</b>	50 g
<b>Linearity</b>	60 g
<b>Linearity 2</b>	100 g
<b>Data transmission type</b>	RS232
<b>Gross Weight</b>	17.600 kg
<b>Product Group</b>	447

### EAN

4045761111165