

N-ISOL. TERMINAL THERMOPLASTIC SCREW
 TERMINAL BLUE, 8MM, SZ 6




Figure similar

| Model | | |
|---|-----------------|---------------|
| Busbar design | | 6x6 mm |
| General technical data | | |
| Insulation material | | thermoplastic |
| Terminal contact spacing | mm | 8 |
| Protection class | | |
| Combustibility class acc. to UL 94 | | others |
| Main circuit | | |
| Operating voltage / Rated value | V | 500 |
| Operating current / Rated value | A | 41 |
| Appearance | | |
| Color | | blue |
| Product details | | |
| Product component / required / connection plate | | No |
| Number | | |
| Number of terminal points | | 1 |
| Connections | | |
| Connectable conductor cross-section / stranded | | |
| • minimum | mm ² | 6 |
| • maximum | mm ² | 6 |
| Connectable conductor cross-section | | |
| • solid | | |

| | | |
|---|-----------------|---|
| — minimum | mm ² | 6 |
| — maximum | mm ² | 6 |
| • finely stranded | | |
| — with core end processing / minimum | mm ² | 6 |
| — with core end processing / maximum | mm ² | 6 |
| — without core end processing / minimum | mm ² | 6 |
| — without core end processing / maximum | mm ² | 6 |

Type of electrical connection screw-type terminals

Mechanical Design

| | | |
|---|----|-------------|
| Height / with lowest-profile installation | mm | 35 |
| Length | mm | 55 |
| Mounting type | | others |
| Material / of the insulating body | | Thermoplast |

General Product Approval

Test Certificates

Shipping Approval



[other](#)



Shipping Approval

other



[Environmental Confirmations](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WA10111NH01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8WA10111NH01/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8WA10111NH01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015