



# MSR Hot Restrike

## MSR 400 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

### Product data


GeniPubl	
Cap-Base	GZZ9.5 [ GZZ9.5]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Studio/Theatre
Life to 50% Failures (Nom)	1000 h
System Description	Hot Restrike
LittPubl	
Color Code	- [ Not Specified]
Luminous Flux (Min)	28500 lm
Luminous Flux (Nom)	32000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	328
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	92
ElecPubl	
Power (Nom)	400 W
Lamp Current (Nom)	6.9 A

Ignition Supply Voltage (Min)	207 V
CntrPubl	
Dimmable	Yes
MechPubl	
Cap-Base Information	-
LDRPubl	
Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C
ProductPubl	
Full product code	871829122796000
Order product name	MSR 400 HR 1CT/4
EAN/UPC - Product	8718291227960
Order code	928050205115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928050205115
Net Weight (Piece)	0.034 kg

# MSR Hot Restrike

## Warnings and Safety

## Dimensional drawing





MSR 400 HR

### Product

MSR 400 HR 1CT/4

## Photometric data



XDPO\_XDMSR\_HR\_--Spectral power distribution Colour

