

Einsatzempfehlung

Material	Stahl N/mm ²			Rostfreie Stähle		Guss		NE-Metalle			Superleg.		Stahl gehärtet		
Zugfestigkeit	<500	<800	<1200 (<HRC38)	<1600 (<HRC48)	<800	<1200	GG	GGG	Al Knetleg.	Al Si<10%	Cu, Ms	Ti/Ni/Co <900	900-1500	HRC 48-57	HRC 58-63
40 00 862 431 - Vc (m/min)	15-35	10-28	10-14		10-14	5-7	28-36	22-30	90	55-70	18-45	10	6		
40 00 862 525 - Vc max.	20-40	15-35	12-15		12-18	6-8	36-45	28-40	70	70-85	28-63	10	6		
Kühlung	Emulsion	Emulsion/Öl	Emulsion/Öl		Öl	Öl	Emulsion	Emulsion	Emulsion	Emulsion	Emulsion/Öl	Öl	Emulsion/Öl		