

ICP303450PA

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
With Safety Circuit

Specifications

Renata Type	ICP303450
IEC Designation	ICP043552
Part Number	100701
Contact Method	Wire AWG 26
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	510 mAh
Minimum Capacity	500 mAh (0.2C cut off 3.0 V at 20°C)

Internal Impedance	< 230 mΩ / 50% SOC
--------------------	--------------------

Thickness (t)	Max 3.5 mm
Length (l)	Max 52.0 mm
Width (w)	Max 34.5 mm
Weight	~ 10.8 g


Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 255 mA
Max. Charging Current	1.0 C CC – 510 mA
Temperature at Charging	0 °C 45 °C

Discharge Characteristic	
Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 1020 mA (for non continues discharge) 1.0 C – 510 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	--

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.