

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-1050QC1	RED	105-125VAC	1.5mA	25,000
WL-1050QC2	CLEAR	105-125VAC	1.5mA	25,000
WL-1050QC3	AMBER	105-125VAC	1.5mA	25,000
WL-1050QC4	WHITE	105-125VAC	1.5mA	25,000
WL-1052QC5	GREEN	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-1051QC1	RED	208-250VAC	1.5mA	25,000
WL-1051QC2	CLEAR	208-250VAC	1.5mA	25,000
WL-1051QC3	AMBER	208-250VAC	1.5mA	25,000
WL-1051QC4	WHITE	208-250VAC	1.5mA	25,000
WL-1053QC5	GREEN	208-250VAC	1.5mA	25,000
INCANDESCENT 12V SERIES				
WL-1090QC1-12V	RED	12V-14V	80mA	25,000
WL-1090QC3-12V	AMBER	12V-14V	80mA	25,000
WL-1090QC4-12V	WHITE	12V-14V	80mA	25,000
WL-1090QC5-12V	GREEN	12V-14V	80mA	25,000
INCANDESCENT 28V SERIES				
WL-1090QC1-28V	RED	24V-28V	40mA	25,000
WL-1090QC3-28V	AMBER	24V-28V	40mA	25,000
WL-1090QC4-28V	WHITE	24V-28V	40mA	25,000
WL-1090QC5-28V	GREEN	24V-28V	40mA	25,000

NOTES


1. Recommended panel thickness
0.030" to 0.090"
2. .187" terminals are standard
3. Storage temperature
 T_{STG} : -25°C - +80°C
4. Ambient temperature
 T_A : -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance
 V_{OP} : ±10%
8. Body material
Nylon, white
9. Lens material
Polycarbonate
10. Bezel material
Stainless steel
11. .250" terminals available upon request

CERTIFICATIONS

UL (E340667), RoHS



DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

