



Designed to meet the requirement of a large capacity fire protection unit for computer diskettes, tapes and all forms of data storage. Suitable for use in commercial business premises for large volume storage.

- **FIRE PROTECTION (DATA)** – Tested to Swedish NT Fire 017-120dis standard, providing 120 minutes fire protection for computer backup tapes.
- **WATER RESISTANCE** – Twin water resistant seals provide an airtight water resistant inner compartment for your computer media.
- **LOCKING** – **DS4620K** – Fitted with a high quality key lock supplied with two keys. **DS4620E** – Fitted with an advanced high security electronic lock with clear LED display, dual control, hidden code & scrambled code that can be programmed as standard. **DS4620F** – Fitted with an advanced high security touchscreen keypad & fingerprint lock with clear LED display, internal alarm, dual control, hidden code and scrambled code that can be programmed as standard with up to 128 fingerprints.
- **DROP TEST** – Fire and impact tested from 9.1 metres for resistance to the impact of falling through the burning floors of a building.
- **SPECIAL FEATURES** – DS4621 and DS4622 are fitted with automatic slam shut locking.
- **FITTINGS** – Each unit comes complete with height adjustable shelves and pull out media trays.
- **COLOUR** – Finished in a high quality scratch resistant white paint RAL9003.
- **GDPR** – Maintain GDPR Compliance at home or in the office by keeping your company's vital and important records secure and protected.



MODEL NUMBER	EXTERNAL DIMENSIONS H x W x D	INTERNAL DIMENSIONS H x W x D	DOOR SWING / HANDLE DEPTH	WEIGHT	CAPACITY	SHELVES / DRAWERS	LTO	DAT	DATA CAPACITY DLT	CD-ROM
DS4621K/E/F	1160 x 690 x 720mm	885 x 400 x 405mm	595mm/40mm	340kg	143 Litres	2/3	294	1276	294	564
DS4622K/E/F	1685 x 690 x 720mm	1410 x 400 x 405mm	595mm/40mm	480kg	228 Litres	2/5	462	1972	462	940
DS4623K/E/F	1685 x 1200 x 720mm	1410 x 800** x 405mm	595mm/40mm	753kg	457 Litres	3/10	924	3944	924	1880
MEDIA DRAWERS	-	60 x 370 x 397mm	-	3kg	-	-	42	116	42	94

** width comprises of two compartments each 395mm wide.



* Ratings are approximate only and may vary due to area conditions and location. Please check with your underwriter.