




## IEC Twist Melt Bolt Thermocouple with Standard Thermocouple Plug Type J or K with 20mm blade tip



### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Type 'J' or 'K' twist melt bolt thermocouple
- Rotational blade style tip allowing correct positioning for reduced resistance in the melt flow
- Widely used in plastics extruders and injection moulders
- Designed to withstand high pressure applications experienced with molten plastics & polymers
- Stainless steel bolt with 1/2" UNF-20 2A thread
- 152mm stem length
- 20mm long blade tip immersion length
- Temperature range to 400°C
- Grounded hot junction
- Standard plug termination (round pin)
- Tolerance & colour code in accordance with IEC-584 specification

T/C Type	Thread	Stem Length	Tip Immersion Length	order code
J	1/2" UNF-20	152mm (6" inch)	20.0mm	XF-945-FAR
K	1/2" UNF-20	152mm (6" inch)	20.0mm	XF-946-FAR

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com