Resistors

TT Electronics

Precision Thin Film Nichrome Chip Resistors

PCF Series

- Precision thin film technology
- Extended ohmic range 1R 3M
- Precision to ±0.01% and 2ppm/°C
- Passivated range for superior humidity performance
- Load life stability and humidity to 0.05%
- Pb-free standard with SnPb option
- AEC-Q200 grade available



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data - Standard Range

Type	TCR (ppm/°C)	Power (W)	Limiting Element			Ohmic Value Range ¹			
. 146	1		Voltage (V)	1% & 0.5%	0.25%	0.1%	0.05%	0.01%	
PCF0201	50 25	0.031	15	49R9-33K 49R9-5K		-			
	50			10R-205K				-	
	25				2011 2031			•••••	
PCF0402	15	0.063	25			49R9-70K	49R9-12K		
PCFU4U2	10 5	0.063	25			49R9-12K 49R9-5K	AQD.	9-3K	
	3					4515-31		.J-3K	
	2						49R9 - 4K99		
	50			2R-	11/1	4R7-1M			
	25			211-	T1A1	41(7-114)	4R7-332K		
PCF0603	15	0.053	50			4R7-332K		-	
PCFU6U3	10 5	0.063	50	_		24R9-15K	24R9-100K		
	3					2413-131		.L	
	2					24R9 – 15K			
	50			1R-	2M	4R7-2M	24R9-200K	_	
	25								
PCF0805	15	0.1	100			4R7-511K		24R9-200	
PCF0805	10 5	0.1	100				24R9-200K	.L	
	3						24R9-30K		
	2								
	50			1R-2	M5	4R7-2M5		_	
	25						4R7-1M		
PCF1206	15	0.125	150			4R7-1M	1M	24R9-500	
PCF1206	10 5	0.125	150						
	3						24R9-49K9		
	3 2								
	50			1R-2	M5	4R7-2M5			
	25								
PCF1210	15	0.2	150			4R7-1M			
FCF1210	10 5 3	0.2	130					-	
	3					24R9-50K			
	2								
	50			1R-	3M	4R7-3M		_	
	25						4R7-1M		
PCF2010	15 10	0.25	150			4R7-1M		24R9-500	
1 0. 2010	5	0.23	130			l	•••••	L	
	3						24R9-100K		
	2								
	50			1R -	3M	4R7-3M		_	
	25			1K – 3W			4R7-1M		
PCF2512	15 10	0.5	150			4R7-1M		24R9-50	
r CFZJ1Z	10 5	0.5	130				L		
	3						24R9-100K		
	3								

Note 1: Standard values E24 or E96. Other values may be available by request.

PCF Series



Electrical Data - AEQ-Q200 Grade - Standard Range

Туре	TCR	Power	Limiting Element		Oh	mic Value Rang	e *		
туре	(ppm/°C)	(W)	Voltage (V)	1%	0.5%	0.25%	0.1%	0.05%	
PCF0402A	50 25	0.063	25		49R9 – 100K				
PCF0603A	50 25	0.063	50	10R – 332K 10				10R – 49K9	
PCF0805A	50 25	0.1	100	10					
PCF1206A	50 25	0.125	150		10R – 1M0				
PCF1210A	50 25	0.25	150						
PCF2010A	50 25	0.25	150	10R					
PCF2512A	50 25	0.5	150						

^{*} Standard values E24 or E96.

Electrical Data - High Power Range

Time	TCR (ppm/°C)	Power (W)	Limiting Element			Ohmic Value Range	*	
Туре	1	Power (w)	Voltage (V)	0.5%	0.25%	0.1%	0.05%	0.01%
	50				4R7-1M			
	25 15					•••••	4R7-332K	24R9-100K
PCF0603H	10	0.1	75	4R7-332K				
1 01 000311	5	0.1	/5	24R9-15				L
	3						2400 454	•
	2				-		24R9-15K	
	50			1	IR-1M	4R7-1M		
	25						4R7-511K	24R9-200K
PCF0805H	15	0.125	150	4R7-332K		•••••		
PCFU8U5H	10 5	0.125	150		4R7-511K 24R9-30K			L
	3					24N3-30K		
	2				-		24R9-30K	
	50							
	25				4R7	7-1M		24R9-500K
	15							24R9-500K
PCF1206H	10	0.25	200			24R9-50K	•••••	
	5 3					2489-308		
	2				-		24R9-49K9	
	50							
	25			4R7-1M				24R9-500K
	15				410	1141		24K9-300K
PCF1210H	10	0.33	200	24R9-50K			L	
	5					24R9-50K	•	•
	3 2				-		24R9-49K9	
	50							
	25				407	7-1M		24R9-500K
	15				407	,-TIVI		24K9-300K
PCF2010H	10	0.33	200			L		
	5					24R9-50K	•••••	•
	3 2				-		24R9-49K9	
	50							
PCF2512H	25	0.75	200		1R-2K	AD	7-2K	24R9-2K
FCFZJ1ZII	15	0.73	200		TU-51/	46	/ - Z IX	Z4NJ-ZN
	10							

^{*} Standard values E24 or E96. Other values may be available by request.

PCF Series



Electrical Data - AEQ-Q200 Grade - High Power Range

Туре	TCR	Power	Limiting Element		Oh	mic Value Rang	e *		
туре	(ppm/°C)	(W)	Voltage (V)	1%	0.5%	0.25%	0.1%	0.05%	
PCF0603HA	50 25	0.1	75		10R – 332K				
PCF0805HA	50 25	0.125	150		10R – 100K				
PCF1206HA	50 25	0.25	200		···				
PCF1210HA	50 25	0.33	200	10R – 1M0					
PCF2010HA	50 25	0.33	200						

Electrical Data - Passivated Range

_	TCR	Power	Limiting Element		Ohmic Value Range *	:	
Туре	(ppm/°C)	(W)	Voltage (V)	0.5%	0.25%	0.1%	
PCF0402P	50 25	0.063	25	25R-25K			
1 CI 04021	15	0.005	23		49R9-12K		
PCF0603P	50 25 15	0.063	50	25R-332K			
PCF0805P	50 25 15	0.1	100	10R - 1M			
PCF1206P	50 25 15	0.125	150	10R-1M			
PCF2010P	50 25 15	0.25	150	10R - 1M5 25R - 1M			
PCF2512P	50 25	0.5	150	• • • • • • • • • • • • • • • • • • • •	10R - 1M5	• • • • • • • • • • • • • • • • • • • •	
	15				25R - 1M		

Precision Thin Film Nichrome Chip Resistors





Physical Data

		Dimens	ions (mm) and	Weight (mg)		
	L	W	T max	Α	С	Wt
0201	0.58 ± 0.05	0.29 ± 0.05	0.26	0.15 ± 0.05	0.12 ± 0.05	0.14
0402	1.0 ± 0.1	0.5 ± 0.05	0.55	0.25 ± 0.15	0.2 ± 0.15	0.54
0603	1.6 ± 0.2	0.8 ± 0.2	0.65	0.35 ± 0.25	0.3 ± 0.2	1.8
0805	2.0 ± 0.2	1.25 <u>+</u> 0.2	0.65	0.4 <u>±</u> 0.25	0.3 <u>±</u> 0.2	4.7
1206	3.05 ± 0.15	1.55 ± 0.15	0.65	0.35 ± 0.25	0.42 ± 0.2	9.0
1210	3.10 ± 0.15	2.5 ± 0.25	0.65	0.55 ± 0.25	0.4 ± 0.3	10
2010	4.9 ± 0.2	2.4 ± 0.25	0.65	0.55 <u>±</u> 0.3	0.6 <u>±</u> 0.3	24
2512	6.3 ± 0.2	3.1 ± 0.25	0.65	0.7 ± 0.45	0.6 ± 0.3	38

Construction

A thin-film material is selectively deposited on a 96% alumina substrate together with metallic contacts at each end of the resistor. The unadjusted resistors are heat treated to give the required TCR and stability, then a precisely controlled laser trim process adjusts the resistance value. Epoxy protection is applied and wrap-around terminations are added and plated with Nickel then Tin. Each resistor is measured immediately before packing into tape.

Terminations

The standard termination is 100% Sn matte plated wrap-around suitable for soldering. SnPb plated option is available for standard range PCF over the restricted range below.

SnPb Termination Option Range

Туре	TCR (ppm/°C)	Power (W)	Limiting Element Voltage (V)	Ohmic Value Range 1% 0.5% 0.25% 0.1%
	50	0.1	100	10R – 250K
PCF0805	25			10R – 100K
	15			10R – 100K
	50			10R – 500K
PCF1206	25	0.125	150	10R – 200K
	15			10R – 200K

Performance Data - Standard Range

Test Parameters	Conditions	Maxi	mum change (+0).05R)
		>0.05% tolerance 0603 to 2512	Chip size 0201, 0402	≤0.05% tolerance 0603 to 2512
Load life	1000 hours rated load @ 70°C	0.25%	0.5%	0.05%
Humidity	1000 hours @ 40°C, 90 - 95%RH		0.3%	0.05%
Short term overload	6.25 x rated Power , or 2 x LEV, for 5 sec	0.5%	0.5%	0.05%
High temperature operation	1000 hours at 125°C	0.25%	0.25%	0.25%
Temperature cycle	5 cycles -55 C, 125°C	0.1%	0.1%	0.05%
Resistance to solder heat	270°C, 10 sec	0.2%	0.2%	0.05%
Solderability	235°C, 2 sec	95% minimum coverage		

Performance Data - High Power Range

Test Parameters	Conditions	Maximum change (+0.05R)
Load life	1000 hours rated load @ 70°C	0.5%
Humidity	1000hrs @ 40°C, 90 - 95%RH	0.5%
Short term overload	6.25 x rated Power, or 2 x LEV, for 5 sec	0.5%
High temperature operation	1000 hours at 155°C	0.5%
Temperature cycle	5 cycles -55°C, 150°C	0.25%
Resistance to solder heat	270°C, 10 sec	0.2%
Solderability	235°C, 2 sec	95% minimum coverage

General Note

BI Technologies IRC Welwyn

Precision Thin Film Nichrome Chip Resistors


PCF Series



Performance Data - Passivated Range

Test Parameters	Conditions	Maximum change (+0.05R)		
		0603 to 2512	0402	
Load life	1000 hours rated load @ 70°C	0.05%	0.25%	
Humidity	1000hrs @ 40°C, 90 - 95%RH	0.05%	0.5%	
Short term overload	6.25 x rated Power, or 2 x LEV, for 5 sec	6.25 x rated Power, or 2 x LEV, for 5 sec 0.02% 0.1		
High temperature operation	1000 hours at 125°C	0.05%	0.5%	
Temperature cycle	5 cycles -55 C, 125°C	0.02%	0.1%	
Resistance to solder heat	270°C, 10 sec	0.02%	0.1%	
Solderability	235°C, 2 sec	95% minimum coverage		

Derating Curve



Solderability

The terminations have an electroplated nickel barrier and tin coating. This ensures excellent 'leach' resistance properties and solderability.

Packaging

PCF Resistors are supplied taped and reeled as as per IEC 286-3. Sizes 2010 and 2512 are in embossed plastic tape. Smaller sizes are in paper tape.

Application Notes

PCF resistors are ideally suited for handling by automatic methods due to their rectangular shape and the small dimensional tolerances. Electrical connection to a ceramic substrate or to a printed circuit board can be made by reflow or wave soldering of wrap-around terminations.

Wrap-around terminations provide good leach properties and ensure reliable contact. Due to the robust construction, the PCF can be immersed in the solder bath for 30 seconds at 260°C. This enables the resistor to be mounted on one side of a printed circuit board and wire-leaded components applied on the other side.

PCF resistors themselves can operate at a maximum temperature of 125° C (see performance above) (155 $^{\circ}$ C for High Power grades). For soldered resistors, the joint temperature should not exceed 110 $^{\circ}$ C. This condition is met when the stated power levels at 70 $^{\circ}$ C are used.

PCF Series



Ordering Procedure

This product has two valid part numbers:

European (Welwyn) Part Number**: PCF0603-11-1K54BI (0603, standard, 15ppm/°C, 1.54 kilohm ±0.1%, Pb-free)



1	2	3	4	5	6	7		
Туре	Size	Range	TCR	Value	Tolerance	Termination	& Packing	
PCF	0201	Omit for	-20 = ±2ppm/°C	E24 = 3/4 characters	L = ±0.01%	A = AEC-Q200	grade, Pb-free	
	0402	Standard	-19 = ±3ppm/°C	E96 = 3/4 characters	$W = \pm 0.05\%$	I = Standard grade, Pb-free		
	0603	H = High Power	-13 = ±5ppm/°C			Standard Packing		
	0805	P = Passivated	-12 = ±10ppm/°C	K = kilohms	$C = \pm 0.25\%$	0201, 0402	10,000/reel	
	1206		-11 = ±15ppm/°C	M = megohms	$D = \pm 0.5\%$	0603 to 1210	5000/reel	
	1210		$R = \pm 25 ppm/^{\circ}C$		F = ±1%	2010, 2512	4000/reel	
	2010		$-02 = \pm 50 \text{ppm/}^{\circ}\text{C}$	·		T1* = Pb-fre	e, 1K reel	
	2512			•		0201 to 1206, 2010, 2512	1000/reel	
						PB = SnP	b, 1K reel	
						0805, 1206	1000/reel	

^{*} Non-standard; enquire to confirm availability

USA (IRC) Part Number*: PCF-W0603LF-11-1541-B-P-LT (0603, standard, 15ppm/°C, 1.54 kilohm ±0.1%, Pb-free)

PCF-	W 0 6 0 3	L F	- 1 1 -	1 5 4 1	- B -	. Р -	LT
1	2	3	4	5	6	7	8

1	2	3	4	5	6	7	8	
Туре	Model	Termination	TCR	Value	Tolerance	Tape	Packing	
PCF	W0201	LF = Pb-free	13 = ±5ppm/°C	3 digits + multiplier	$T = \pm 0.01\%$	P = Paper	LT = Tape & Reel	
	W0402	(100%Sn)	12 = ±10ppm/°C	R = ohms for	$A = \pm 0.05\%$	(0201 to 1210)	0201, 0402	10,000/reel
	W0603		11 = ±15ppm/°C	values <100 ohms	$B = \pm 0.1\%$	E = Embossed	0603 to 1210	5000/reel
	W0805		03 = ±25ppm/°C		$C = \pm 0.25\%$	(2010, 2512)	2010, 2512	4000/reel
	W1206		02 = ±50ppm/°C		$D = \pm 0.5\%$			
	W1210				F = ±1%			
	W2010					-		

^{*} Applies only to Standard Range, Pb-Free parts

W2512

^{**} Applies to all Ranges, Termination and Packing options.