# **PRODUCT** C17180\_YASMEEN-30-RS

### YASMEEN-30-RS

~11° spot beam

#### **SPECIFICATION:**

**Dimensions** Height **ROHS** compliant Ø 29.7 mm 18.2 mm yes 🕕

## **MATERIALS:**

Component

YASMEEN-30-RS

Type

Single lens

Material

**PMMA** 

Colour

clear

**Finish** 

1/8

## **ORDERING INFORMATION:**

Component

C17180\_YASMEEN-30-RS


» Box size: 480 x 280 x 300 mm

Qty in box MOQ MPQ Box weight (kg) 792 132 66 5.1

Published: 21/10/2020 Last update: 13/02/2023 Subject to change without prior notice



## PRODUCT DATASHEET C17180\_YASMEEN-30-RS



See also our general installation guide: www.ledil.com/installation\_guide




## **OPTICAL RESULTS (MEASURED):**

bridgelux.

LED Vesta TW 6mm DP FWHM / FWTM 19.0° / 49.0°

 $\begin{array}{ll} {\sf Efficiency} & 83 \ \% \\ {\sf Peak intensity} & 3.6 \ {\sf cd/lm} \end{array}$ 

LEDs/each optic 1
Light colour White
Required components:



Published: 21/10/2020






LED V3 HD Gen 8  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 14.0° / 30.0° Efficiency 95 % Peak intensity 10 cd/lm

LEDs/each optic Light colour White


Required components:



#### bridgelux

LED V4 HD Gen 7 FWHM / FWTM 16.0° / 34.0° Efficiency 94 % Peak intensity 7.5 cd/lm LEDs/each optic 1 White Light colour


Required components:



#### bridgelux

V6 HD Gen 7 LED FWHM / FWTM 20.0° / 46.0° Efficiency 93 % Peak intensity 4.4 cd/lm LEDs/each optic 1 Light colour White

Required components:




## **CITIZEN**

Required components:

CLU700/701/702/703

FWHM / FWTM 22.0° / 48.0° Efficiency 93 % Peak intensity 4.1 cd/lm LEDs/each optic White Light colour



Published: 21/10/2020



## **CITIZEN**

LED CLU710/711


FWHM / FWTM 24.0° / 60.0°

Efficiency 87 %

Peak intensity 2.2 cd/lm LEDs/each optic 1

Light colour White

Required components:



## **CITIZEN**

LED CLU7A2/7A3

FWHM / FWTM 18.0° / 34.0°


Efficiency 94 %

Peak intensity 7.3 cd/lm

LEDs/each optic 1

Light colour White

Required components:



## **CITIZEN**

LED CLU7B2

FWHM / FWTM 14.0° / 29.0°

Efficiency 95 %


Peak intensity 10.4 cd/lm

1

Light colour White

Required components:

LEDs/each optic



#### CREE - LED

LED CMA1303


FWHM / FWTM 16.0° / 38.0°

Efficiency 94 %

Peak intensity 6.5 cd/lm

LEDs/each optic 1
Light colour White

Required components:








LED XHP35 HI  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 14.0° / 26.0° Efficiency 95 % Peak intensity 13.3 cd/lm LEDs/each optic


Light colour White Required components:



#### CREE & LED

LED XM-L FWHM / FWTM 14.0° / 28.0° Efficiency 94 % Peak intensity 11.5 cd/lm


LEDs/each optic 1 White Light colour Required components:



#### CREE + LED

LED XP-G2 FWHM / FWTM 11.4° / 20.8° Efficiency 92 % Peak intensity 22.7 cd/lm LEDs/each optic 1


Light colour White Required components:



## **WNICHIA**

LED NCSxE17A FWHM / FWTM 10.0° / 22.0° Efficiency 92 % Peak intensity 16.5 cd/lm LEDs/each optic White Light colour

Required components:



Published: 21/10/2020







# PRODUCT DATASHEET C17180\_YASMEEN-30-RS

#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

## Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

www.ledil.com/ where\_to\_buy