

SVJC solid carbide boring bar, positive
for longitudinal and copy turning using VC indexable inserts

ATORN[®]



Application

for longitudinal and copy turning with VC indexable insert 35°.

Version

- precision-manufactured **cemented carbide** boring bar, with inner cooling, C type, 52° pitch angle, 35° tip angle, 7° clearance angle

Advantage

- slender geometry for longitudinal and copy turning
- positive body geometry ensures low cutting forces

Art. No.	17827 632
ISO name	E 10K SVJC R/L 07
Min. bore diameter	13 mm
Shaft diameter	10 mm
Clearance length	18 mm
Length	125 mm
Clamping surface height	9 mm
Programming size	1.5 mm
Suitable for indexable inserts	VC.. 0702..
Tool design	Left

EAN-Code

4050293449693