

shrink-fit extensions with IC

with straight shank

ATORN[®]

Application

For extending and reducing to smaller diameters.

Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel



Art. No.	23431 644
Clamping diameter	10 mm
Outer diameter	32 mm
Tapered diameter	22 mm
Length	150 mm
Max. clamp in depth	42 mm
Min. clamp in depth	32 mm
Max. adjustment travel	10 mm
Setting screw size	M8 x 1 mm
Width across flats	3 mm

EAN-Code

40502934 18255