



Model Number

LCR 18-3,2-0,5-K2

Glass fiber optic - diffuse with PVC covering

Threading M8

Features

- M8 x 1 thread

Series

Fiber optic amplifiers

Device series VL18LL
VariKont M

Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Technical data

General specifications

Fiber optic length	l	500 mm
Fiber optic diameter	d	5 mm
Adapter form		18
End piece		thread
Bending radius		min. 25 mm (static)
Fiber bundle diameter		2.3 mm
Fiber configuration	Fv	optical seperated
Approvals		CE
Angle of divergence		68 °

Ambient conditions

Ambient temperature	-20 ... 85 °C (-4 ... 185 °F) [Adapter]
	-20 ... 85 °C (-4 ... 185 °F) [End head and Covering]
Storage temperature	-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Protection degree	IP65
Material	
Optical face	glass
Sheathing	PVC
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PBT
Extraction force	100 N

Dimensions

