



**100%
Recycled**



▼ **Description**

DCP Green is the first 100 % recycled paper for colour laser printing of office documents. Its high level of whiteness and its extremely high opacity guarantee duplex printing. Its smooth surface and excellent flatness allow for clean and crisp presentations. Its sheet formation optimizes printing of both text and image.

DCP Green laser guarantees an excellent machine running, generates no dust and has a longer archival life thanks to the DIN 6738 norm.

DCP Green is Blue Angel and Ecolabel certified.

Paper certifications



www.blauer-engel.de/uz14a



Mill certifications

ISO 14001

ISO 9001

Version 141

▼ **Technical specifications**

Substance	<i>g/m²</i>	90	100	120	160	200	250	NF EN ISO 536
Thickness	<i>µm</i>	95	105	126	168	200	250	NF EN ISO 534
Bulk	<i>cm³/g</i>	1,05	1,05	1,05	1,05	1,00	1,00	NF EN ISO 534
Brightness	<i>CIE</i>	145	145	145	145	145	145	NF ISO 11475
Bekk smoothness	<i>s</i>	110	110	110	110	110	110	NF ISO 5627
Absolute humidity	<i>%H₂O</i>	4.5	4.5	4.5	4.5	4.5	4.5	NF EN ISO 20287
Relative humidity	<i>% in the air</i>	30	30	30	30	30	30	Sword measurement
Opacity	<i>%</i>	95	97	98	99	>99	>99	NF ISO 2471
Formation index	<i>Indice on 120</i>	100	100	100	100	100	90	Kajaani measurement
Permanence		DIN 6738 CL 24-85						

*These values are not contractual
Revision date : 03/04/2020*