

FOODLUBE DISMANTLING SPRAY

Page: 1

Compilation date: 09/02/2015

Revision No: 9

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FOODLUBE DISMANTLING SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC24: Lubricants, greases, release products.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House Swillington

Leeds

West Yorkshire LS26 8BS ENGLAND

Tel: +44 (0) 113 232 2700 **Fax:** +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Aerosol 2: H223; -: H229

Classification under CHIP: -: R10

Most important adverse effects: Flammable aerosol. Pressurised container: May burst if heated.

2.2. Label elements

Label elements under CLP:

Hazard statements: H223: Flammable aerosol.

H229: Pressurised container: May burst if heated

Signal words: Warning

Hazard pictograms: GHS02: Flame



Precautionary statements: P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Pressurized container: Do not pierce or burn, even after use.

FOODLUBE DISMANTLING SPRAY

Page: 2

P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P211: Do not spray on an open flame or other ignition source.

P285: In case of inadequate ventilation wear respiratory protection.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

CARBON DIOXIDE AEROSOL PROPELLANT

EINECS	CAS	CHIP Classification	CLP Classification	Percent
204-696-9	124-38-9	Substance with a Community workplace exposure limit.	Press. Gas: H280	2-10%

PHOSPHATE ALKYL AMINE DERIVATIVE

279-632-6	80939-62-4	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319;	<2%
			Aquatic Chronic 2: H411	

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.Eye contact: Bathe the eye with running water for 15 minutes.Ingestion: Wash out mouth with water. Do not induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Carbon dioxide. Dry chemical powder. Alcohol resistant foam. Do not use water.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

FOODLUBE DISMANTLING SPRAY

Page: 3

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of

ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for

disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep away from direct sunlight.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

CARBON DIOXIDE AEROSOL PROPELLANT

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5000ppm 9150mg/m3	15000ppm 27400mg/m3	-	•

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure all engineering measures

mentioned in section 7 of SDS are in place.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Protective gloves.

Eye protection: Safety glasses with side-shields.

FOODLUBE DISMANTLING SPRAY

Page: 4

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Pale yellow

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Oily

Boiling point/range°C: >100 Flash point°C: 60 - 93

Autoflammability°C: >200 Relative density: <1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

FOODLUBE DISMANTLING SPRAY

Page: 5

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, FLAMMABLE

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

Packing group: 2.1

14.5. Environmental hazards

Environmentally hazardous: No Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

FOODLUBE DISMANTLING SPRAY

Page: 6

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: Contains only FDA listed ingredients. NSF H1 registered.

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on

the approximation of the laws of Member States relating to aerosol dispensers.

This safety data sheet is prepared in accordance with Commission Regulation (EU) No

453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H223: Flammable aerosol.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

R10: Flammable.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

FOODLUBE DISMANTLING SPRAY

Page: 7

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = phycico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.