

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1601116006](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, with Connector Position Assurance, Black

Documents:

3D Model	Packaging Specification 1601118000-000 (PDF)
Drawing (PDF)	Packaging Specification 1601118002-000 (PDF)
3D Model (PDF)	Packaging Specification 1601119000-000 (PDF)
Product Specification 1601110001-PS-000 (PDF)	Datasheet (PDF)
Application Specification 1601110001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	160111
Application	Power, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056821681

Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	20.104/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	1601110001-AS-000
Packaging Specification	1601118000-000, 1601118002-000, 1601119000-000
Product Specification	1601110001-PS-000
Sales Drawing	1601110000-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[160111](#) Series

Mates With

MX150 Hybrid Sealed Male Connector
Assembly [160112](#)

Use With

MX150 Female Terminal [33012](#) , [33001](#)

Industry Standard Terminal 2.80mm