

Twist drill type H with soldered cemented carbide insert 4xD

For hard machining up to 63 HRC

ORION[®]

Application:

Hard machining up to 63 HRC.

Execution:

- Twist drill with universal standard geometry, soldered cemented carbide insert (K20) and driving lug on the clamp shank

Advantage:

- Cemented carbide insert, K20, for a long service life
- polished chipping spaces ensure good chip removal
- long service life in hardened steel



Art. no.	11162 065
Brand	ORION
Manufacturer Part Number	11162065
Cutting edge diameter	6.5 mm
Chip flute length	32 mm
Length	71 mm
f hard 65 HRC	0.07 mm/r
DIN	8037
Gross Weight	0.016 kg
Product Group	140

EAN

4039247030255