## I30H012

Part Number



- Increased switching distance
- Innovative ASIC circuit technology
- Integrated error display
- Minimal mounting clearance thanks to wenglor weproTec

**Technical Data** 

recillical Data				
Inductive Data				
Switching Distance	35 mm			
Correction Factors Stainless Steel V2A/CuZn/Al	1,00/0,42/0,39			
Mounting	non-flush			
Mounting A/B/C/D in mm	55/82/105/35			
Mounting B1 in mm	080			
Switching Hysteresis	< 10 %			
Electrical Data				
Supply Voltage	1030 V DC			
Current Consumption (Ub = 24 V)	< 12 mA			
Switching Frequency	140 Hz			
Temperature Drift	< 10 %			
Temperature Range	-4080 °C			
Switching Output Voltage Drop	< 1 V			
Switching Output/Switching Current	150 mA			
Residual Current Switching Output	< 100 µA			
Short Circuit Protection	yes			
Reverse Polarity and Overload Protection	yes			
Protection Class III				
Mechanical Data				
Housing Material	CuZn, nickel-plated			
Degree of Protection	IP67			
Connection	M12 × 1; 4-pin			
Safety-relevant Data				
MTTFd (EN ISO 13849-1)	3706,54 a			
Function				
Error Indicator	yes			
PNP NO/NC antivalent	•			
Connection Diagram No.	101			
uitable Connection Equipment No.				
Suitable Mounting Technology No.	130			


**wepro**Tec


Inductive Sensors with increased switching distances are distinguished by rugged design, easy installation and reliable measured values. The large range makes additional types of sensor superfluous because they can also be used to implement special applications. In addition to error-free operation of several sensors in a very small space, the new generation also provides the possibility of detecting system errors before it's too late thanks to ASIC und wenglor weproTec.

## **Complementary Products**

PNP-NPN Converter BG2V1P-N-2M







_egen	ıa		PT	Platinum measuring resistor	ENARS422	Encoder A/Ā (TTL)	
+	Supply Voltage +		nc	not connected	ENBR5422	Encoder B/B (TTL)	
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B	
Α	Switching Output	(NO)	W	Trigger Input	Amin	Digital output MIN	
Ā	Switching Output	(NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX	
٧	Contamination/Error Output	(NO)	0	Analog Output	Аок	Digital output OK	
V	Contamination/Error Output	(NC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input		Awv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance	
S	Shielding		b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path		SY	Synchronization	Wire Co	Wire Colors according to DIN IEC 757	
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black	
RDY	Ready		E+	Receiver-Line	BN	Brown	
GND	Ground		S+	Emitter-Line	RD	Red	
CL	Clock		±	Grounding	OG	Orange	
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow	
•	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue	
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey	
Signal	Signal Output		Mag	Magnet activation	WH	White	
BI_D+/-	Ethernet Gigabit bidirect. data	line (A-D)	RES	Input confirmation	PK	Pink	
	Encoder 0-pulse 0-0 (TTL)	. ,	EDM	Contactor Monitoring	GNYE	Green/Yellow	

## Mounting

